



General Information

Series	C24
Dielectric	Metallized Polypropylene
Style	Radial
RoHS	Yes
Lead	Wire Leads
Typical Component Weight	3.56 g
Miscellaneous	Rated current = 0.05A.

Dimensions

L	26.5mm +0.3mm
H	16mm +0.1mm
T	7mm +0.2mm
S	22.5mm +/-0.4mm
LL	25mm +2/-1mm
F	0.8mm +/-0.05mm

Specifications

Capacitance	0.33 uF
Tolerance	10%
Voltage AC	400 VAC
Temperature Range	-40/+85°C
Rated Temperature	85°C
Max dV/dt	50 V/us

Packaging Specifications

Packaging	Bulk, Bag
-----------	-----------