



Click [here](#) for the 3D model.

General Information

Series	CC 01005
Style	SMD Chip
Description	SMD, MLCC, High Voltage
RoHS	Yes
Termination	Tin
Halogen Free	Yes
MSL	1

Dimensions

L	0.4mm +/-0.02mm
W	0.2mm +/-0.02mm
T	0.2mm +/-0.02mm
B	0.105mm +/-0.035mm
Case Code (EIA / mm)	01005 / 0402

Packaging Specifications

Packaging	T&R, 180mm, Plastic Tape
Packaging Quantity	20000

Specifications

Capacitance	2.7 pF
Tolerance	+/-0.25 pF
Voltage DC	25 VDC
Temperature Range	-55/+125°C
Temp. Coefficient	COG
Dissipation Factor	0.22%
Insulation Resistance	10 GOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.