



Click [here](#) for the 3D model.

### General Information

Series	CS
Style	SMD Chip
Features	Class II
RoHS	Yes
Termination	Flexible Termination

### Dimensions

L	1.6mm +/-0.2mm
W	0.8mm +/-0.1mm
T	0.8mm +/-0.1mm
B	0.425mm +/-0.225mm
Case Code (EIA / mm)	0603 / 1608

### Packaging Specifications

Packaging	T&R, 178mm, Paper Tape
Packaging Quantity	4000

### Specifications

Capacitance	0.047 uF
Tolerance	10%
Voltage DC	50 VDC
Temperature Range	-55/+125°C
Temp. Coefficient	X7R
Dissipation Factor	3.5%
Insulation Resistance	10 GOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.