



General Information

Gruppe	EFF4
Typ	Sheet
Beschreibung	Flex Suppressor Flame Retardant Type
Eigenschaften	Flame Retardant Type
RoHS	Yes
Zulassungen	UL94 V-0, UL File No.E176124, AEC-Q200
Umfeld	RoHS Compliant, Halogen Free, PVC Free, Lead Free, Red Phosphorus Free

Dimensions

Blattgröße	240x80mm
L	240mm NOM
W	80mm NOM
T	0.5mm NOM

Packaging Specifications

Banddicke	0.03 mm
Gewicht	36.3 g

Specifications

Temperaturbereich	-40/+125°C
Magnetische Permeabilität	140 u At 3MHz
Effektive Frequenz	1 MHz to 3GHz
Spezifisches Gewicht	3.7 TYP
Leitfähigkeit	1.52 typical
Oberflächenwiderstand	1 MOhm/sq. TYP

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.