Sample Kit Contents


Part Number	Size	TC	Capacitance	Voltage	Tolerance	Quantity
CC0805JRNPO9BN100	0805	NPO	10pF	50V	±5%	40
CC0805JRNPO9BN120	0805	NPO	12pF	50V	±5%	40
CC0805JRNPO9BN150	0805	NPO	15pF	50V	±5%	40
CC0805JRNPO9BN180	0805	NPO	18pF	50V	±5%	40
CC0805JRNPO9BN200	0805	NPO	20pF	50V	±5%	40
CC0805JRNPO9BN220	0805	NPO	22pF	50V	±5%	40
CC0805JRNPO9BN270	0805	NPO	27pF	50V	±5%	40
CC0805JRNPO9BN330	0805	NPO	33pF	50V	±5%	40
CC0805JRNPO9BN470	0805	NPO	47pF	50V	±5%	40
CC0805JRNPO9BN680	0805	NPO	68pF	50V	±5%	40
CC0805JRNPO9BN101	0805	NPO	100pF	50V	±5%	40
CC0805JRNPO9BN221	0805	NPO	220pF	50V	±5%	40
CC0805JRNPO9BN331	0805	NPO	330pF	50V	±5%	40
CC0805JRNPO9BN471	0805	NPO	470pF	50V	±5%	40
CC0805JRNPO9BN561	0805	NPO	560pF	50V	±5%	40
CC0805JRNPO9BN681	0805	NPO	680pF	50V	±5%	40
CC0805JRNPO9BN821	0805	NPO	820pF	50V	±5%	40
CC0805JRNPO9BN102	0805	NPO	1nF	50V	±5%	40
CC0805KRX7R7BB224	0805	X7R	220nF	16V	±10%	40
CC0805KKX7R7BB474	0805	X7R	470nF	16V	±10%	40
CC0805KRX7R8BB224	0805	X7R	220nF	25V	±10%	40
CC0805KKX7R8BB334	0805	X7R	330nF	25V	±10%	40
CC0805KKX7R8BB474	0805	X7R	470nF	25V	±10%	40
CC0805KKX7R8BB684	0805	X7R	680nF	25V	±10%	40
Part Number	**Size**	**TC**	**Capacitance**	**Voltage**	**Tolerance**	**Quantity**


Sample Kit Contents cont.

Part Number	Size	TC	Capacitance	Voltage	Tolerance	Quantity
CC0805KRX7R9BB101	0805	X7R	100pF	50V	±10%	40
CC0805KRX7R9BB221	0805	X7R	220pF	50V	±10%	40
CC0805KRX7R9BB331	0805	X7R	330pF	50V	±10%	40
CC0805KRX7R9BB471	0805	X7R	470pF	50V	±10%	40
CC0805KRX7R9BB561	0805	X7R	560pF	50V	±10%	40
CC0805KRX7R9BB681	0805	X7R	680pF	50V	±10%	40
CC0805KRX7R9BB102	0805	X7R	1nF	50V	±10%	40
CC0805KRX7R9BB152	0805	X7R	1.5nF	50V	±10%	40
CC0805KRX7R9BB222	0805	X7R	2.2nF	50V	±10%	40
CC0805KRX7R9BB332	0805	X7R	3.3nF	50V	±10%	40
CC0805KRX7R9BB472	0805	X7R	4.7nF	50V	±10%	40
CC0805KRX7R9BB682	0805	X7R	6.8nF	50V	±10%	40
CC0805KRX7R9BB103	0805	X7R	10nF	50V	±10%	40
CC0805KRX7R9BB153	0805	X7R	15nF	50V	±10%	40
CC0805KRX7R9BB223	0805	X7R	22nF	50V	±10%	40
CC0805KRX7R9BB273	0805	X7R	27nF	50V	±10%	40
CC0805KRX7R9BB333	0805	X7R	33nF	50V	±10%	40
CC0805KRX7R9BB473	0805	X7R	47nF	50V	±10%	40
CC0805KRX7R9BB683	0805	X7R	68nF	50V	±10%	40
CC0805KRX7R9BB104	0805	X7R	100nF	50V	±10%	40
CC0805KRX7R9BB154	0805	X7R	150nF	50V	±10%	40
CC0805KKX7R9BB224	0805	X7R	220nF	50V	±10%	40
CC0805KKX7R9BB334	0805	X7R	330nF	50V	±10%	40
CC0805KKX7R9BB474	0805	X7R	470nF	50V	±10%	40
Part Number	**Size**	**TC**	**Capacitance**	**Voltage**	**Tolerance**	**Quantity**

Scope

This product specification is applied to Multi-layer Ceramic Capacitor used for Automotive application .





Revision History

Revision	Date	Change notification	Description
Version 0	Nov, 02, 2026	-	- New datasheet, Engineering Kit for CC0805000000SB000 CC 0805 series.