



Click [here](#) for the 3D model.

General Information

Series	BEAD L
Style	Through-Hole
RoHS	Yes

Dimensions

D	3.4mm +/-0.2mm
L	13mm MAX
LL	20mm MIN
S	5mm NOM
L2	4.4mm +/-0.2mm
F	0.65mm NOM

Packaging Specifications

Packaging	T&R
Packaging Quantity	2000
Typical Component Weight	400 mg

Specifications

Temperature Range	-20/+70°C
-------------------	-----------