



Click [here](#) for the 3D model.

#### General Information

|        |              |
|--------|--------------|
| Series | BEAD L       |
| Style  | Through-Hole |
| RoHS   | Yes          |

#### Dimensions

|    |                |
|----|----------------|
| D  | 3.4mm +/-0.2mm |
| L  | 13mm MAX       |
| LL | 20mm MIN       |
| S  | 5mm NOM        |
| L2 | 4.4mm +/-0.2mm |
| F  | 0.65mm NOM     |

#### Packaging Specifications

|                          |        |
|--------------------------|--------|
| Packaging                | T&R    |
| Packaging Quantity       | 2000   |
| Typical Component Weight | 400 mg |

#### Specifications

|                   |           |
|-------------------|-----------|
| Temperature Range | -20/+70°C |
|-------------------|-----------|