

## C1808C331KHRACTU

Aliases (C1808C331KHRAC7800)

SMD Comm X7R HV, Ceramic, 330 pF, 10%, 3,000 VDC, X7R, SMD, MLCC, High Voltage, Temperature Stable, 1808 / 4520



Click [here](#) for the 3D model.

### General Information

|                          |   |
|--------------------------|---|
| Series                   | SMD Comm X7R HV                             |
| Style                    | SMD Chip                                    |
| Description              | SMD, MLCC, High Voltage, Temperature Stable |
| Features                 | High Voltage                                |
| RoHS                     | Yes   |
| Termination              | Tin   |
| Marking                  | No  |
| Typical Component Weight | 100 mg                                      |
| Shelf Life               | 78 Weeks                                    |
| MSL                      | 1   |

### Specifications

|  |   |
|--|---|
| Capacitance  | 330 pF  |
| Measurement Condition  | 1 kHz 1.0Vrms                                   |
| Tolerance  | 10%   |
| Voltage DC   | 3000 VDC  |
| Dielectric Withstanding Voltage                                    | 3,600 VDC                                       |
| Temperature Range  | -55/+125°C                                      |
| Temp. Coefficient  | X7R   |
| Capacitance Change with Reference to +25°C and 0 VDC Applied (TCC) | 15%, 1kHz 1.0Vrms                               |
| Dissipation Factor   | 2.5% 1 kHz 1.0Vrms                              |
| Aging Rate   | 3% Loss/Decade Hour: Referee Time is 1000 Hours |
| Insulation Resistance  | 100 GOhms                                       |

### Dimensions

|                      |                 |
|----------------------|-----------------|
| L                    | 4.7mm +/-0.5mm  |
| W                    | 2mm +/-0.2mm    |
| T                    | 2mm +/-0.15mm   |
| S                    | 2.9mm MIN       |
| B                    | 0.6mm +/-0.35mm |
| Case Code (EIA / mm) | 1808 / 4520     |

### Packaging Specifications

|                    |                          |
|--------------------|--------------------------|
| Packaging          | T&R, 180mm, Plastic Tape |
| Packaging Quantity | 1000                     |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.