



Threaded Mounting Stud  
D < 60: M8 x 12  
D ≥ 60: M12 x 16

Note: Please contact KEMET for case type

Click [here](#) for the 3D model.

**General Information**

Series	C93
Dielectric	Metallized Polypropylene
Style	Can
Features	Single Phase PFC
RoHS	Yes
Lead	Fast On (2+2)
Typical Component Weight	195 g
Miscellaneous	Contact KEMET for case type and additional dimensional data.

**Dimensions**

D	40mm +/-0.5mm
L	78mm +/-2mm
S	13.4mm NOM

**Packaging Specifications**

Packaging	Bulk, Bag
Packaging Quantity	62

**Specifications**

Capacitance	10 uF
Tolerance	-5/+15%
Voltage DC	600 VDC
Voltage AC	415 VAC
Temperature Range	-25/+55°C
Rated Temperature	55°C
Max dV/dt	30 V/us
Ripple Current	1.7 Amps
Irms	1.7 A

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.