



Click [here](#) for the 3D model.

General Information

Series	CC NPO
Style	SMD Chip
Features	Consumer equipment, Industrial Equipment, Mobile Electronics, Infotainment/comfort equipment
RoHS	Yes
Termination	Tin

Dimensions

L	0.6mm +/-0.03mm
W	0.3mm +/-0.03mm
T	0.3mm +/-0.03mm
B	0.15mm +/-0.05mm
Case Code (EIA / mm)	0201 / 0603

Packaging Specifications

Packaging	T&R, 178mm, Paper Tape
Packaging Quantity	15000

Specifications

Capacitance	1.8 pF
Tolerance	+/-0.05 pF
Voltage DC	25 VDC
Temperature Range	+20/+125°C
Temp. Coefficient	COG
Dissipation Factor	0.23%

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.