




General Information

Series	CS
Style	SMD Chip
Features	Automotive, Soft Termination
RoHS	Yes
Termination	Flexible Termination
Halogen Free	Yes

Dimensions

L	3.2mm +/-0.4mm
W	1.6mm +/-0.2mm
B	0.25mm MIN
Case Code (EIA / mm)	1206 / 3216

Packaging Specifications

Packaging	T&R, 180mm, Plastic Tape
-----------	--------------------------

Specifications

Capacitance	6,800 pF
Tolerance	10%
Voltage DC	250 VDC
Temperature Range	-55/+125°C
Temp. Coefficient	X7R
Insulation Resistance	10 GOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.