



General Information

Series	FS
Style	Sheet
Description	Flex Suppressor Flame Retardant Type
Features	Flame Retardant Type
RoHS	Yes
Qualifications	UL94 V-0, UL File No. E176124
Environment	RoHS Compliant, Halogen Free, PVC Free, Lead Free, Red Phosphorus Free

Dimensions	
Sheet Size	240x80mm
L	240mm NOM
W	80mm NOM
T	0.1mm NOM

Packaging Specifications	
Adhesive Thickness	0.01 mm
Typical Component Weight	10.83 g

Specifications	
Temperature Range	-40/+105°C
Permeability	10 u At 10MHz
Effective Frequency	3 GHz to 40GHz
Specific Gravity	4.5 TYP
Thermal Conductivity	1.17 typical
Surface Resistivity	100 MOhm/sq. TYP

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.