



Click [here](#) for the 3D model.

General Information

| | |
|----------------------|---------------------------------|
| Series | GTX |
| Style | Plastic Box |
| Description | EMI Filter, With Y Capacitor |
| Features | Single-phase |
| Phase | Single-phase |
| RoHS | With Exemptions |
| Qualifications | UL, cUL, TUV |
| Tightening Torque | 1.2 ~ 1.4N-m (Recommended) |
| Line Terminal | 14-4(JST) |
| Line Terminal Width | 12 Max. |
| Earth Terminal | R5.5-4(JST) |
| Earth Terminal Width | 9.5 Max. |
| Miscellaneous | 60 K Self-Temperature Rise Max. |
| Terminal Type | Screw |

Dimensions

| | |
|----|-----------------|
| L | 75mm +/-1mm |
| W | 44mm +/-1mm |
| H | 25mm +/-1mm |
| S | 17.6mm NOM |
| L1 | 66.7mm +/-0.5mm |
| W1 | 35mm +/-0.5mm |

Packaging Specifications

| | |
|--------------------------|-------|
| Packaging | Box |
| Packaging Quantity | 30 |
| Typical Component Weight | 128 g |

Specifications

| | |
|-------------------|------------|
| Voltage AC | 250 VAC |
| Voltage DC | 560 VDC |
| Rated Current | 16 A |
| Ripple Current | 16 A |
| Temperature Range | -25/+105°C |
| Leakage Current | 1 mA |