



Click [here](#) for the 3D model.

General Information

Series	P410
Dielectric	Metallized Paper
Style	Radial
Features	RC Unit approved
RoHS	Yes
Termination	Cut (Tinned Wire)
Lead	Cut
Qualifications	ENEC, UL, cUL
Construction	Molded
Typical Component Weight	3.42 g
Miscellaneous	Resistor Tolerance: +/-30%. Resistor= 100 Ohms.

Specifications

Capacitance	0.033 uF
Tolerance	20%
Voltage DC	1000 VDC
Voltage AC	300 VAC
Temperature Range	-40/+85°C
Rated Temperature	85°C
Insulation Resistance	3 GOhms
Safety Class	X1

Dimensions

L	18.5mm MAX
H	14.3mm MAX
T	8.5mm MAX
S	15.2mm +/-0.4mm
LL	6mm -1mm
F	0.8mm +/-0.05mm

Packaging Specifications

Packaging	Bulk, Bag
Packaging Quantity	500

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.