



Note: '()' correspond to the letters used in the product bulletin

Click [here](#) for the 3D model.

#### General Information

Series	PEG227
Dielectric	Aluminum Electrolytic
Style	Axial
Description	Vibration Resistant Ultra High CV Aluminum Electrolytic
RoHS	Yes
Lead	Wire Leads
Qualifications	AEC-Q200
Halogen Free	Yes
Typical Component Weight	16 g
Shelf Life	156 Weeks

#### Dimensions

D	18.2mm +/-0.5mm
L	38.7mm +/-1mm
L1	45mm MIN
LL	40mm +/-2mm
F	1mm +/-0.03mm

#### Packaging Specifications

Packaging	Tray
-----------	------

#### Specifications

Capacitance	1,900 uF
Tolerance	-10/+30%
Voltage DC	63 VDC, 54 VDC (150C)
Temperature Range	-40/+150°C
Rated Temperature	125°C
Life	8400 Hrs (Rated Voltage At 125C), 2000 Hrs (Rated Voltage At 150C)
ESR	47 mOhms (100Hz 20C), 21 mOhms (100kHz 20C), 11.8 mOhms (5-100kHz 150C)
Ripple Current	18.2 Amps (5kHz 125C, With Heat Sink), 11.5 Amps (5kHz 140C, With Heat Sink), 5.1 Amps (5kHz 150C, With Heat Sink), 7.2 Amps (5kHz 125C), 9.1 Amps (5kHz 125C Max)
Leakage Current	363.1 uA (5min 20°C)