
SC2211KKX7RWBB152

Please contact sales for availability

SC, Ceramic, 1,500 pF, 10%, 250 VAC, X7R, SMD, MLCC, Safety Cap, 2211 / 5628



General Information	
Series	SC
Style	SMD Chip
Description	SMD, MLCC, Safety Cap
RoHS	Yes
Termination	Tin
MSL	1

Dimensions	
L	5.7mm +/-0.4mm
W	2.8mm +/-0.3mm
T	2.5mm +/-0.3mm
B	0.525mm +/-0.225mm
Case Code (EIA / mm)	2211 / 5628

Specifications	
Capacitance	1,500 pF
Tolerance	10%
Temperature Range	-55/+125°C
Temp. Coefficient	X7R
Dissipation Factor	2.5%
Insulation Resistance	10 GOhms

Packaging Specifications	
Packaging	T&R, 180mm, Plastic Tape
Packaging Quantity	500

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

© 2006 - 2026 YAGEO