



Click [here](#) for the 3D model.

**General Information**

Series	SCC
Style	Snap-In
Description	Radial Cylindrical Double Layer Capacitor
RoHS	Yes
Lead	2 Pin
Construction	Organic Electrolyte
Typical Component Weight	54.5 g

Dimensions	
D	30mm +/-1.5mm
L	55mm +/-3mm
S	10mm +/-0.5mm
LL	5.8mm +/-0.5mm

  

Packaging Specifications	
Packaging	Carton Box
Packaging Quantity	100

Specifications	
Capacitance	300 F
Tolerance	30%
Voltage DC	2.7 VDC
Temperature Range	-40/+70°C
Rated Temperature	70°C
ESR	5.5 mOhms (1kHz), 8 mOhms (Max DC IEC)
Leakage Current	0.6 uA (72 Hrs)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.