



Click [here](#) for the 3D model.

#### General Information

Series	SCF-J/JH
Style	Through-Hole
Features	High Impedance, Space Saving
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 55 K.
Core	Nanocrystal

#### Dimensions

D	70mm MAX
T	39mm
H	38mm MAX
LL	5mm +/-2mm
S	44mm NOM
S1	32mm NOM
Wire Size	1.8mm x 3 Parallel

#### Packaging Specifications

Packaging	Tray
Packaging Quantity	36
Typical Component Weight	192.7 g

#### Specifications

Voltage AC	500 VAC
Inductance	4 mH
Rated Current	40 A
Temperature Range	-40/+120°C
DC Resistance	2.1 mOhms