



Click [here](#) for the 3D model.

#### General Information

Series	SC47X 3PHASE
Style	Through-Hole
Features	High Inductance, High Permeability
RoHS	Yes
Miscellaneous	Temperature Rise (K) Reference: 60.
Core	Nanocrystal

#### Dimensions

D	63mm MAX
T	45mm MAX
H	61mm MAX
LL	4.5mm +/-1.5mm
S	25mm NOM
S1	35mm NOM

#### Packaging Specifications

Packaging	Tray
Packaging Quantity	27
Typical Component Weight	234 g

#### Specifications

Voltage AC	250 VAC
Voltage DC	320 VDC
Inductance	2.15 mH
Rated Current	30 A
Temperature Range	-40/+130°C
DC Resistance	2.31 mOhms