



Click [here](#) for the 3D model.

General Information

Series	SCR Three Phase
Style	Through-Hole
Features	High Impedance, Space Saving
RoHS	Yes
Miscellaneous	70 (K) Temperature Rise Max.
Core	Mn-Zn Ferrite

Dimensions

D	50mm MAX
H	28mm MAX
LL	3.5mm +/-0.5mm
S	44mm NOM
Wire Size	1.4mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	60
Typical Component Weight	100 g

Specifications

Voltage AC	500 VAC
Voltage DC	500 VDC
Inductance	1.5 mH
Rated Current	13 A
Temperature Range	-25/+120°C
DC Resistance	9.2 mOhms