



Click [here](#) for the 3D model.

General Information

Series	SCT
Style	Snap-In
Description	Radial Cylindrical Double Layer Capacitor
RoHS	Yes
Lead	2 Pin
Construction	Organic Electrolyte
Typical Component Weight	75 g

Dimensions	
D	35mm +/-1.5mm
L	60mm +/-3mm
S	10mm +/-0.5mm
LL	5.8mm +/-0.5mm

Packaging Specifications	
Packaging	Carton Box
Packaging Quantity	45

Specifications	
Capacitance	360 F
Tolerance	30%
Voltage DC	2.7 VDC
Temperature Range	-40/+85°C
Rated Temperature	85°C
ESR	4 mOhms (1kHz), 5.4 mOhms (Max DC IEC)
Leakage Current	0.8 uA (72 Hrs)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.