

SN10-500

Aliases (UALSN105000000)

Differential Mode Chokes - Power, KEMET, SN, Through-Hole, Normal Mode, 110 uH, MIN



Click [here](#) for the 3D model.

General Information

Series	SN
Style	Through-Hole
Features	Compact Size
RoHS	Yes
Miscellaneous	26 (K) Temperature Rise Max.
Core	Fe

Dimensions	
D	21mm MAX
H	12mm MAX
LL	20mm +/-2mm
S	10mm
L2	1.5mm MAX
Wire Size	0.8mm

Specifications	
Inductance	110 uH
Inductance Tolerance	MIN
Rated Current	3 A
Temperature Range	-40/+105°C
DC Resistance	52 mOhms

Packaging Specifications	
Packaging	Bulk
Packaging Quantity	1000
Typical Component Weight	11.8 g

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.