



Click [here](#) for the 3D model.

General Information

Series	SN-J
Style	Through-Hole
RoHS	Yes
Miscellaneous	Temperature Rise Maximum: 45 K.
Core	Fe

Dimensions

D	33mm MAX
T	21mm MAX
H	33.5mm MAX
LL	4.5mm +/-1mm
S	16mm NOM
Wire Size	1.5mm

Specifications

Inductance	108 uH
Rated Current	8 A
Temperature Range	-40/+120°C
DC Resistance	0.027 Ohms

Packaging Specifications

Packaging	Tray
Typical Component Weight	44.9 g

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.