



Click [here](#) for the 3D model.

**General Information**

Series	SS11VL
Style	Through-Hole Bobbin
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 45 K.
Core	Mn-Zn Ferrite

**Dimensions**

L	22mm +/-1mm
T	14.5mm +/-1mm
H	19.5mm +/-1mm
LL	3.5mm +/-1mm
S	13mm +/-0.5mm
S1	10mm +/-0.5mm
Wire Size	0.2mm
F	0.8mm +/-0.1mm

**Specifications**

Voltage AC	250 VAC
Inductance	82 mH
Rated Current	300 mA
Temperature Range	-40/+120°C
DC Resistance	4.1 Ohms

**Packaging Specifications**

Packaging	Tray
Packaging Quantity	600
Typical Component Weight	10.5 g

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.