



Click [here](#) for the 3D model.

#### General Information

Series	SSHB21HS
Style	Through-Hole
RoHS	Yes
Notes	Marking: R20 Lot No.
Miscellaneous	Temperature Rise Maximum: 55 K.
Core	Mn-Zn Ferrite

#### Dimensions

L	26mm MAX
T	23mm MAX
H	15.5mm MAX
LL	3.5mm +/-0.5mm
S	21mm +/-0.5mm
S1	15mm NOM
Wire Size	0.45mm
F	0.8mm NOM

#### Packaging Specifications

Packaging	Tray
Packaging Quantity	360
Typical Component Weight	14 g

#### Specifications

Voltage AC	250 VAC, 320 VAC (IEC60664-1)
Rated Current	2 A
Temperature Range	-40/+120°C
DC Resistance	0.14 Ohms (Per Line)
Inductance Common Mode	7.1 mH
Inductance Differential Mode	96 uH