



Click [here](#) for the 3D model.

#### General Information

|               |   |
|---------------|---|
| Series        | SSRH24NV/NH   |
| Style         | Through-Hole Bobbin                                       |
| Features      | Compact Size, Light Weight, Low Rdc, Ultra-High Impedance |
| RoHS          | Yes   |
| Miscellaneous | Temperature Rise Maximum: 65 K.                           |
| Core          | Mn-Zn Ferrite   |

#### Dimensions

|           |                |
|-----------|----------------|
| L         | 25.5mm MAX     |
| T         | 20mm MAX       |
| H         | 31mm MAX       |
| LL        | 3.5mm +/-0.5mm |
| S         | 13mm NOM       |
| S1        | 10mm NOM       |
| Wire Size | 0.75mm         |
| F         | 0.8mm +/-0.5mm |

#### Packaging Specifications

|                          |      |
|--------------------------|------|
| Packaging                | Tray |
| Packaging Quantity       | 240  |
| Typical Component Weight | 25 g |

#### Specifications

|                   |            |
|-------------------|------------|
| Voltage AC        | 250 VAC    |
| Inductance        | 4.1 mH     |
| Rated Current     | 5 A        |
| Temperature Range | -40/+120°C |
| DC Resistance     | 0.035 Ohms |