



Click [here](#) for the 3D model.

General Information

| | |
|---------------|---|
| Series | SSRH24NVS/NHS |
| Style | Through-Hole Bobbin |
| Features | Compact Size, Light Weight, High Performance, Low Rdc |
| RoHS | Yes |
| Miscellaneous | Temperature Rise Maximum: 65 K. |
| Core | Mn-Zn Ferrite |

Dimensions

| | |
|-----------|----------------|
| L | 25.5mm MAX |
| T | 20mm MAX |
| H | 31mm MAX |
| LL | 3.5mm +/-0.5mm |
| S | 13mm NOM |
| S1 | 10mm NOM |
| Wire Size | 0.6mm |
| F | 0.8mm +/-0.5mm |

Packaging Specifications

| | |
|--------------------------|------|
| Packaging | Tray |
| Packaging Quantity | 200 |
| Typical Component Weight | 25 g |

Specifications

| | |
|-------------------|------------|
| Voltage AC | 250 VAC |
| Inductance | 8 mH |
| Rated Current | 3.5 A |
| Temperature Range | -40/+120°C |
| DC Resistance | 0.074 Ohms |