
C244N3700AA02J

Obsolete

C24, Film, Metallized Polypropylene, Motor Run, 0.7 uF, 5%, 85°C, 22.5 mm



General Information	
Series	C24
Dielectric	Metallized Polypropylene
Style	Radial
RoHS	Yes
Lead	Cut
Typical Component Weight	5.88 g
Miscellaneous	Rated current = 0.11A.

Dimensions	
L	26.5mm +0.3mm
H	18.5mm +0.1mm
T	10mm +0.2mm
S	22.5mm +/-0.4mm
LL	4mm +2mm
F	0.8mm +/-0.05mm

Specifications	
Capacitance	0.7 uF
Tolerance	5%
Voltage AC	400 VAC
Temperature Range	-40/+85°C
Rated Temperature	85°C
Max dV/dt	50 V/us

Packaging Specifications	
Packaging	Bulk, Bag

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

© 2006 - 2026 YAGEO