Sample Kit Contents

Part Number	Category	Size	TC	Capacitance	Voltage	Tolerance	Quantity
CQ0805BRNPOYBNR20	HiQ	0805	NPO	0.2pF	250 V	±0.1pF	40
CQ0805BRNPOYBNR30	HiQ	0805	NPO	0.3pF	250 V	±0.1pF	40
CQ0805BRNPOYBNR40	HiQ	0805	NPO	0.4pF	250 V	±0.1pF	40
CQ0805BRNPOYBNR50	HiQ	0805	NPO	0.5pF	250 V	±0.1pF	40
CQ0805BRNPOYBNR60	HiQ	0805	NPO	0.6pF	250 V	±0.1pF	40
CQ0805BRNPOYBNR70	HiQ	0805	NPO	0.7pF	250 V	±0.1pF	40
CQ0805BRNPOYBNR80	HiQ	0805	NPO	0.8pF	250 V	±0.1pF	40
CQ0805BRNPOYBNR90	HiQ	0805	NPO	0.9pF	250 V	±0.1pF	40
CQ0805BRNPOYBN1R0	HiQ	0805	NPO	1.0pF	250 V	±0.1pF	40
CQ0805BRNPOYBN1R1	HiQ	0805	NPO	1.1pF	250 V	±0.1pF	40
CQ0805BRNPOYBN1R2	HiQ	0805	NPO	1.2pF	250 V	±0.1pF	40
CQ0805BRNPOYBN1R3	HiQ	0805	NPO	1.3pF	250 V	±0.1pF	40
CQ0805BRNPOYBN1R5	HiQ	0805	NPO	1.5pF	250 V	±0.1pF	40
CQ0805BRNPOYBN1R6	HiQ	0805	NPO	1.6pF	250 V	±0.1pF	40
CQ0805BRNPOYBN1R8	HiQ	0805	NPO	1.8pF	250 V	±0.1pF	40
CQ0805BRNPOYBN2R0	HiQ	0805	NPO	2.0pF	250 V	±0.1pF	40
CQ0805BRNPOYBN2R2	HiQ	0805	NPO	2.2pF	250 V	±0.1pF	40
CQ0805BRNPOYBN2R4	HiQ	0805	NPO	2.4pF	250 V	±0.1pF	40
CQ0805BRNPOYBN2R7	HiQ	0805	NPO	2.7pF	250 V	±0.1pF	40
CQ0805BRNPOYBN3R3	HiQ	0805	NPO	3.3pF	250 V	±0.1pF	40
CQ0805BRNPOYBN3R6	HiQ	0805	NPO	3.6pF	250 V	±0.1pF	40
CQ0805BRNPOYBN3R9	HiQ	0805	NPO	3.9pF	250 V	±0.1pF	40
CQ0805BRNPOYBN4R3	HiQ	0805	NPO	4.3pF	250 V	±0.1pF	40
CQ0805BRNPOYBN4R7	HiQ	0805	NPO	4.7pF	250 V	±0.1pF	40
Part Number	**Category**	**Size**	**TC**	**Capacitance**	**Voltage**	**Tolerance**	**Quantity**


Sample Kit Contents cont.

Part Number	Category	Size	TC	Capacitance	Voltage	Tolerance	Quantity
CQ0805CRNPOYBN5R6	HiQ	0805	NPO	5.6pF	250 V	±0.25pF	40
CQ0805CRNPOYBN6R2	HiQ	0805	NPO	6.2pF	250 V	±0.25pF	40
CQ0805CRNPOYBN6R8	HiQ	0805	NPO	6.8pF	250 V	±0.25pF	40
CQ0805CRNPOYBN7R0	HiQ	0805	NPO	7.0pF	250 V	±0.25pF	40
CQ0805CRNPOYBN7R5	HiQ	0805	NPO	7.5pF	250 V	±0.25pF	40
CQ0805CRNPOYBN8R0	HiQ	0805	NPO	8.0pF	250 V	±0.25pF	40
CQ0805CRNPOYBN8R2	HiQ	0805	NPO	8.2pF	250 V	±0.25pF	40
CQ0805CRNPOYBN9R0	HiQ	0805	NPO	9.0pF	250 V	±0.25pF	40
CQ0805CRNPOYBN9R1	HiQ	0805	NPO	9.1pF	250 V	±0.25pF	40
CQ0805JRNPOYBN100	HiQ	0805	NPO	10pF	250 V	±5%	40
CQ0805JRNPOYBN120	HiQ	0805	NPO	12pF	250 V	±5%	40
CQ0805JRNPOYBN150	HiQ	0805	NPO	15pF	250 V	±5%	40
CQ0805JRNPOYBN180	HiQ	0805	NPO	18pF	250 V	±5%	40
CQ0805JRNPOYBN220	HiQ	0805	NPO	22pF	250 V	±5%	40
CQ0805JRNPOYBN270	HiQ	0805	NPO	27pF	250 V	±5%	40
CQ0805JRNPOYBN330	HiQ	0805	NPO	33pF	250 V	±5%	40
CQ0805JRNPOYBN470	HiQ	0805	NPO	47pF	250 V	±5%	40
CQ0805JRNPOYBN560	HiQ	0805	NPO	56pF	250 V	±5%	40
CQ0805JRNPOYBN680	HiQ	0805	NPO	68pF	250 V	±5%	40
CQ0805JRNPOYBN820	HiQ	0805	NPO	82pF	250 V	±5%	40
CQ0805JRNPOYBN101	HiQ	0805	NPO	100pF	250 V	±5%	40
Part Number	**Category**	**Size**	**TC**	**Capacitance**	**Voltage**	**Tolerance**	**Quantity**

Scope

This product specification is applied to Multi-layer Ceramic Capacitor used for Automotive application .





Revision History

Revision	Date	Change notification	Description
Version 0	Nov, 02, 2026	-	- New datasheet, Engineering Kit for CQ0805000000SB000 0805 HiQ series.