BEBE00201210R47MMS

Please contact sales for more information

PULSE, BEBE, Metal Composite, 20%, 470 nH



General Information	
Series	BEBE
Style	SMD Molded
Core	Metal Composite
Description	Closed Magnetic Circuit Type Molding Processing & for Ultra High Current
RoHS	Yes

Dimensions	
L	2mm +/-0.2mm
W	1.2mm +/-0.2mm
T	1mm MAX

Packaging Specifications	
Packaging	T&R
Packaging Quantity	3000

Specifications	
Inductance	0.47 uH
Inductance Tolerance	20%
Saturation Current	5.8 Amps (Isat)
Temperature Range	-55/+125°C

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

© 2006 - 2026 YAGEO