



Click [here](#) for the 3D model.

General Information

类别	A768
电介质	Polymer Aluminum
样式	SMD Can
描述	Surface Mount, Polymer Aluminum
RoHS	Yes
引线	V-Chip
认证	AEC-Q200
AEC-Q200	Yes
无卤	Yes

Dimensions

D	8mm +/-0.5mm
L	6.7mm +/-0.3mm
W	8.3mm +/-0.2mm
H	8.3mm +/-0.2mm
C	9mm +/-0.2mm
P	3.1mm NOM
R	0.5 - 0.8mm

Specifications

容值	220 uF
容差	20%
直流电压	20 VDC, 23 VDC (Surge)
温度范围	-55/+125°C
额定温度	125°C
寿命	2000 Hrs
等效串联电阻 (ESR)	29 mOhms (100kHz 20C)
电流	1600 mAmps (100kHz 125C)
高温焊料	Yes
漏电流	880 uA (2min 20°C)

Packaging Specifications

包装	T&R, 380mm
包装数量	1000

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.