

C961U222MWWDAAWL40

Obsolete

C900AS SFTY X1-760 Y1-500, Ceramic, 2,200 pF, 20%, 760 VAC (X1), 500 VAC (Y1), Y5U, 10 mm





The measurement position of Lead Spacing (S) and Width (V) is critical in straight lead capacitors.

General Information	
Series	C900AS SFTY X1-760 Y1-500
Style	Radial Disc
RoHS	Yes
Termination	Tin
Failure Rate	N/A
Qualifications	VDE, ENEC, UL, cUL
Halogen Free	Yes
Typical Component Weight	1.6 g

Click here for the 3D model.

Dimensions	
D	13mm MAX
T	7mm MAX
S	10mm +/-1mm
LL	4mm +/-1mm
F	0.55mm +/-0.1mm
G	3mm MAX

Packaging Specifications	
Packaging	Bulk, Bag
Packaging Quantity	500

Specifications	
Capacitance	2,200 pF
Tolerance	20%
Voltage AC	760 VAC (X1), 500 VAC (Y1)
Dielectric Withstanding Voltage	4,000 VDC
Temperature Range	-40/+125°C
Temp. Coefficient	Y5U
Dissipation Factor	2.5%
Insulation Resistance	10 GOhms
Safety Class	X1/Y1

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

© 2006 - 2026 YAGEO