


[Click here for the 3D model.](#)
General Information

类别	PME295/P295
电介质	Metallized Paper
样式	Radial
特征	EMI Safety
RoHS	Yes
端子	Tinned Wire
引线	Wire Leads
安全等级	Y1
认证	ENECA, UL, cUL, CQC
AEC-Q200	No
典型元件重量	3.5 g
其他	SRF= 22 MHz.

Dimensions

L	18mm MAX
H	16mm MAX
T	8.5mm MAX
S	15mm +/-0.4mm
LL	30mm +5mm
F	0.8mm +/-0.05mm
G	0.5mm NOM

Specifications

容值	4,700 pF
容差	20%
直流电压	1500 VDC
AC 电压	440 VAC (Y1) (ENECA), 480 VAC (UL, cUL)
温度范围	-40/+115°C
额定温度	115°C
损耗因数	1.3% 1kHz
绝缘阻抗	12 GOhms
最大 dV/dt	2,000 V/us

Packaging Specifications

包装	Bulk, Bag
包装数量	250

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.