

## R71VN42204030K

Aliases (71VN42204030K)

R71, Film, Metallized Polypropylene, General Purpose, 2.2 uF, 10%, 520 VDC, 105°C, 22.5 mm



Click [here](#) for the 3D model.

### General Information

Series	R71
Dielectric	Metallized Polypropylene
Style	Radial
Features	PFC and Pulse
RoHS	Yes
Termination	Tinned Wire
Lead	Wire Leads
Typical Component Weight	9.09 g
Miscellaneous	Above 105C DC And AC Voltage Derating Is 4%/C.

### Dimensions

L	26.5mm +0.3/-0.5mm
H	22mm +0.1/-0.5mm
T	13mm +0.2/-0.5mm
S	22.5mm +/-0.4mm
LL	30mm +5mm
F	0.8mm +/-0.05mm

### Packaging Specifications

Packaging	Bulk, Bag
Packaging Quantity	200

### Specifications

Capacitance	2.2 uF
Tolerance	10%
Voltage DC	520 VDC
Voltage AC	250 VAC
Temperature Range	-40/+110°C
Rated Temperature	105°C
Dissipation Factor	0.1% 25C
Insulation Resistance	13.6364 GOhms
Max dV/dt	120 V/us
ESR	43.4 mOhms (100kHz)
Ripple Current	2.49 Amps (100kHz 85C), 264 Amps (Peak)
Inductance	18 nH

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.