



Click [here](#) for the 3D model.

#### General Information

|                          |                              |
|--------------------------|------------------------------|
| Series                   | R47 X2 520 VAC               |
| Dielectric               | Metallized Polypropylene     |
| Style                    | Radial                       |
| Features                 | Automotive Grade, EMI Safety |
| RoHS                     | Yes                          |
| Termination              | Tinned Wire                  |
| Lead                     | Wire Leads                   |
| Safety Class             | X2                           |
| Qualifications           | AEC-Q200, ENEC, UL, cUL      |
| THB Performance          | No                           |
| Typical Component Weight | 2.2 g                        |

#### Dimensions

|    |                    |
|----|--------------------|
| L  | 18mm +0.3/-0.5mm   |
| H  | 17.5mm +0.1/-0.5mm |
| T  | 6mm +0.2/-0.5mm    |
| S  | 15mm +/-0.4mm      |
| LL | 25mm +2/-1mm       |
| F  | 0.6mm +/-0.05mm    |

#### Packaging Specifications

|                    |           |
|--------------------|-----------|
| Packaging          | Bulk, Bag |
| Packaging Quantity | 700       |

#### Specifications

|                       |              |
|-----------------------|--------------|
| Capacitance           | 0.047 uF     |
| Tolerance             | 20%          |
| Voltage DC            | 1000 VDC     |
| Voltage AC            | 520 VAC (X2) |
| Temperature Range     | -40/+85°C    |
| Rated Temperature     | 85°C         |
| Dissipation Factor    | 0.1% 1kHz    |
| Insulation Resistance | 100 GOhms    |
| Max dV/dt             | 600 V/us     |