



Click [here](#) for the 3D model.

### General Information

Hersteller	YAGEO
Gruppe	RC
Typ	SMD Chip
Beschreibung	Standard Thick Film Chip Resistors
RoHS	Yes
Terminierung	Tin
Haltbarkeit	104 Weeks
Chip Size / Footprint	0603 / 1608

### Dimensions

L	1.6mm +/-0.1mm
W	0.8mm +/-0.1mm
T	0.45mm +/-0.1mm
B1	0.25mm +/-0.15mm
B2	0.25mm +/-0.15mm

### Packaging Specifications

Verpackung	T&R, 178mm
------------	------------

### Specifications

Widerstand (Widerstände)	7.87 Ohms
Widerstandstoleranz	1%
Leistung	0.1W (70C)
Temperaturkoeffizient (Widerstände)	-/+200 ppm/C
Temperaturbereich	-55/+155°C
Gleichspannung	75 V (Max Continuous Voltage at Full Rated Power), 150 Max Over Voltage, 150 Dielectric Withstanding Voltage

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.