


SCF21X-070-S0R9A009JH

Aliases (UALSCF21XS009H)

Common Mode Chokes - Power, KEMET, SC21X 3PHASE, Through-Hole, Common Mode, 1,170 uH



General Information	
Series	SC21X 3PHASE
Style	Through-Hole
Features	High Inductance, High Permeability
RoHS	Yes
Miscellaneous	Temperature Rise (K) Maximum: 70.
Core	Nanocrystal

Click here for the 3D model.

Dimensions	
D	33mm MAX
Н	30mm MAX
LL	4mm +/-0.5mm
Wire Size	0.9mm
Packaging Specifications	

Packaging Specifications	
Packaging	Tray
Packaging Quantity	210
Typical Component Weight	28.7 g

500 VAC
500 VDC
1.17 mH
7 A
-40/+130°C
14.7 mOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 11/21/2025 © 2006 - 2025 YAGEO