


Click [here](#) for the 3D model.

General Information

类别	T340
电介质	MnO ₂ Tantalum
样式	Radial Molded
描述	Radial, Solid Tantalum, Molded
RoHS	No
Prop 65	WARNING: Cancer and reproductive harm - https://www.p65warnings.ca.gov/.
SCIP 编号	a3b4e2e1-63ea-439e-a89a-743225502a7d
端子	Lead (SnPb)
AEC-Q200	No
结构	Molded
其他	Includes Standoff Height of 0.38 +/- 0.13mm.
注释	Longest Lead Is Positive.

Dimensions

W	7.3mm MAX
H	10.5mm MAX
T	4.3mm MAX
S	5mm +/- 0.5mm
LL	15mm +/- 2mm
F	0.5mm +/- 0.03mm

Specifications

容值	22 uF
容差	20%
直流电压	16 VDC (85C), 10 VDC (125C), 0.16 VDC (125C Reverse)
温度范围	-55/+125°C
损耗因数	6%
漏电流	4 uA

Packaging Specifications

包装	Bulk, Bag
包装数量	200

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.