



Click [here](#) for the 3D model.

#### General Information

Series	SSR21NVS-M/NHS-M
Style	Through-Hole Bobbin
Features	High Performance, High Impedance, Strong Inductance
RoHS	Yes
Miscellaneous	60 (K) Temperature Rise Max.
Core	Mn-Zn Ferrite

#### Dimensions

L	23mm MAX
T	23mm MAX
H	14.5mm MAX
LL	3.5mm +/-0.5mm
S	10mm +/-0.5mm
S1	18.5mm +/-0.5mm
Wire Size	0.55mm
F	0.8mm NOM

#### Packaging Specifications

Packaging	Tray
Packaging Quantity	420
Typical Component Weight	13 g

#### Specifications

Voltage AC	250 VAC
Inductance	4.1 mH
Rated Current	3 A
Temperature Range	-40/+120°C
DC Resistance	0.07 Ohms