Innovative Service Around the Globe YAGEO

DATA SHEET

GAS DISCHARGE TUBES
TELEPHONE INTERFACE

2R-5-UT5HT series

RoHS compliant & free



Product specification– June 01, 2026 V.1

Gas Discharge Tube (GDT) Data Sheet

Features




- Provide ultra-fast response to surge voltage from slow-rising surge of 100V/s to rapid-rising surge of 1KV/μs.
- Stable breakdown voltage.
- High insulation resistance.
- Low capacitance (≤1.0pF)
- High holdover voltage
- Large absorbing transient current capability.
- Micro-Gap Design
- Size: 5.4mm*5.0mm
- Operational temperature: -40℃ ~ +125℃
- Meets MSL level 1, per J-STD-020
- Safety certification: UL

Applications


- Repeaters, Modems.
- Telephone Interface, Line cards.
- Data communication equipment.
- Line test equipment

Part Number Code



Dimensions

M Type




Recommended Pad Size

Symbol	Dimension (mm)	
	Spec.	Tolerance
D	5.4	±0.2
T	5.0	±0.2
B	0.5	±0.2

Electrical Characteristics

Part Number	DC Spark-over Voltage	Maximum Impulse Spark-over Voltage	Nominal Impulse Discharge Current	Alternating Discharge Current	Minimum Insulation Resistance		Maximum Capacitance	Device Marking Code
	100V/s	1000V/μs	8/20μs ±5times	50Hz,1sec	Test Voltage	(GΩ)	1MHz	
	(V)	(V)	(KA)	(A)	DC(V)		(pF)	
2RM075M-5-UT5HT	75±20%	650	10.0	5.0	25	1.0	1.0	None
2RM090M-5-UT5HT	90±20%	600	10.0	5.0	50	1.0	1.0	None
2RM150M-5-UT5HT	150±20%	700	10.0	5.0	50	1.0	1.0	None
2RM230M-5-UT5HT	230±20%	750	10.0	5.0	100	1.0	1.0	None
2RM250M-5-UT5HT	250±20%	750	10.0	5.0	100	1.0	1.0	None
2RL300M-5-UT5HT	300±20%	800	5.0	5.0	100	1.0	1.0	None
2RL350M-5-UT5HT	350±20%	900	5.0	5.0	100	1.0	1.0	None
2RL400M-5-UT5HT	400±20%	1000	5.0	5.0	100	1.0	1.0	None
2RL470M-5-UT5HT	470±20%	1100	5.0	5.0	250	1.0	1.0	None
2RL600M-5-UT5HT	600±20%	1500	5.0	5.0	250	1.0	1.0	None
2RL800M-5-UT5HT	800±20%	1800	5.0	5.0	250	1.0	1.0	None
2RL1000M-5-UT5HT	1000±20%	2000	5.0	5.0	500	1.0	1.0	None
2RK1200M-5-UT5HT	1200±20%	2400	3.0	3.0	500	1.0	1.0	None
2RK1500M-5-UT5HT	1500±20%	2800	3.0	3.0	500	1.0	1.0	None


Electrical Ratings

Items	Test Condition/Description	Requirement
DC Spark-over Voltage	The voltage is measured with voltage ramp dv/dt=100V/s.	To meet the specified value
Maximum Impulse Spark-over Voltage	The maximum impulse spark-over voltage is measured with voltage ramp dv/dt=1000V/μs.	
Impulse Discharge Current	Maximum 8/20μs surge current that can be applied between two electrodes, 5 positive and 5 negative surges, with 3 minutes interval time. 	

Alternating Discharge Current	Rated RMS value of AC current at 50Hz, 1 sec. for 10 times with interval time 3 min.	
Insulation Resistance	The resistance of gas tube shall be measured between two electrodes.	
Capacitance	The capacitance of gas tube shall be measured between two electrodes. Test frequency: 1MHz	

Recommended Soldering Conditions

Reflow Soldering




Recommended Conditions

Profile Feature	Pb-Free Assembly
Average ramp-up rate (T_L to T_P)	3℃/second max.
Preheat -Temperature Min ($T_{S\ min}$) -Temperature Max ($T_{S\ max}$) -Time (min to max) (ts)	 150℃ 200℃ 60-180 seconds
$T_{S\ max}$ to T_L -Ramp-up Rate	 3℃/second max.
Time maintained above: -Temperature (T_L) -Time (t_L)	 217℃ 60-150 seconds
Peak Temperature (T_P)	260℃
Time within 5℃ of actual Peak Temperature (t_P)	20-40 seconds
Ramp-down Rate	6℃/second max.
Time 25℃ to Peak Temperature	8 minutes max.


Packaging

Tape



Symbol	Dimension (mm)	
	Spec.	Tolerance
W	12.00	±0.20
P0	4.00	±0.10
P	12.00	±0.10
P1	2.00	±0.10
D	1.55	±0.1
E	1.75	±0.10
F	5.50	±0.10
A0	5.80	±0.10
B0	5.40	±0.10
K0	5.80	±0.10
t	0.50	±0.10

Reel



D	330.00	±1.00
d	13.00	±0.50
L	20.00	±0.50
t	2.00	±0.20

Quantity: 800pcs

Legal Disclaimer

YAGEO, its distributors and agents (collectively, “YAGEO”), hereby disclaims any and all liabilities for any errors, inaccuracies or incompleteness contained in any product related information, including but not limited to product specifications, datasheets, pictures and/or graphics. YAGEO may make changes, modifications and/or improvements to product related information at any time and without notice.

YAGEO makes no representation, warranty, and/or guarantee about the fitness of its products for any particular purpose or the continuing production of any of its products. To the maximum extent permitted by law, YAGEO disclaims (i) any and all liability arising out of the application or use of any YAGEO product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for a particular purpose, non -infringement and merchantability.

YAGEO products are designed for general purpose applications under normal operation and usage conditions. Please contact YAGEO for the applications listed below which require especially high reliability for the prevention of defects which might directly cause damage to the third party's life, body or property: Aerospace equipment (artificial satellite, rocket, etc.), Atomic energy-related equipment, Aviation equipment, Disaster prevention equipment, crime prevention equipment, Electric heating apparatus, burning equipment, Highly public information network equipment, data-processing equipment , Medical devices, Military equipment, Power generation control equipment, Safety equipment, Traffic signal equipment, Transportation equipment and Undersea equipment, or for any other application or use in which the failure of YAGEO products could result in personal injury or death, or serious property damage. Particularly **YAGEO Corporation and its affiliates do not recommend the use of commercial, automotive, and/or COTS grade products for high reliability applications or manned space flight.**

Information provided here is intended to indicate product specifications only. YAGEO reserves all the rights for revising this content without further notification, as long as products are unchanged. Any product change will be announced by PCN.