Innovative Service Around the Globe YAGEO


DATA SHEET

ELECTROSTATIC DISCHARGE PROTECTION DEVICES

INDUSTRIAL / CONSUMER

SCS08CXXL07 SERIES

RoHS compliant & Halogen free





Product specification– October 12, 2022 V.3

Electrostatic Discharged Protection Devices (ESD) Data Sheet

Description

Brightking's SCS08CXXL07 series are designed to protect sensitive electronics from damage or latch-up due to ESD. They are available with operating data and signal lines, such as RS232, I^2C ports, etc.
The series features transient overvoltage protection for up to seven lines using only one package. The series meet the immunity requirements of IEC61000 Level 4 (15KV air, 8KV contact discharge).




Contact : ±8kV
Air : ±15kV



Features

- IEC61000-4-2 ESD 15KV Air, 8KV contact compliance
- SOIC-08 surface mount package
- Protects seven I/O lines
- Peak power dissipation of 300W under 8/20μs waveform
- Working voltage: 15V, 24V
- Low leakage current
- Low capacitance and clamping voltage
- Solid-state silicon avalanche technology
- Lead Free/RoHS compliant
- Solder reflow temperature: Pure Tin-Sn, 260~270℃
- Flammability rating UL 94V-0
- Meets MSL level 1, per J-STD-020



Pin Configuration

Applications

- RS-232 and RS-422 data line protection
- Microprocessor based equipment
- LAN/WAN equipment
- Notebooks, desktops, serves
- I^2C serial ports
- Set Top Box (STB)
- Serial and Parallel ports
- Instrumentation
- Peripherals

Maximum Ratings

Rating	Symbol	Value	Unit
Peak pulse power (tp=8/20μs waveform)	P_{PP}	300	W
ESD voltage (Contact discharge)	V_{ESD}	±8	KV
ESD voltage (Air discharge)		±15	
Storage & operating temperature range	T_{STG} ,T_J	-55~+150	℃

Electrical Characteristics (T_J=25℃)

SCS08C15L07 (Marking: B SM15C-7)

Parameter	Symbol	Condition	Min.	Typ.	Max.	Unit
Reverse stand-off voltage	V_{RWM}				15	V
Reverse breakdown voltage	V_{BR}	I_{BR}=1mA	16.7			V
Reverse leakage current	I_R	V_R=15V each I/O pin			1	μA
Clamping voltage (tp=8/20μs)	V_C	I_{PP}=1A			27	V
Peak Pulse Current(tp=8/20μs)	I_{PP}				10	A
Off state junction capacitance	C_J	0Vdc,f=1MHz Between I/O pins and GND			75	pF

Electrical Characteristics (T_J=25℃)

SCS08C24L07 (Marking: B SM24C-7)

Parameter	Symbol	Condition	Min.	Typ.	Max.	Unit
Reverse stand-off voltage	V_{RWM}				24	V
Reverse breakdown voltage	V_{BR}	I_{BR}=1mA	26.7			V
Reverse leakage current	I_R	V_R=24V each I/O pin			1	μA
Clamping voltage (tp=8/20μs)	V_C	I_{PP}=1A			43	V
Peak Pulse Current(tp=8/20μs)	I_{PP}				2	A
Off state junction capacitance	C_J	0Vdc,f=1MHz Between I/O pins and GND			50	pF

Typical Characteristics Curves

Figure 1. Power Derating Curve




Figure 2. Pulse Waveforms






Figure 3. Non-Repetitive Peak Pulse vs. Pulse Time



Recommended Soldering Conditions


Reflow Soldering



Recommended Conditions

Profile Feature	Pb-Free Assembly
Average ramp-up rate (T_L to T_P)	3℃/second max.
Preheat -Temperature Min ($T_{S\ min}$) -Temperature Max ($T_{S\ max}$) -Time (min to max) (ts)	 150℃ 200℃ 60-180 seconds
$T_{S\ max}$ to T_L -Ramp-up Rate	3℃/second max.
Time maintained above: -Temperature (T_L) -Time (t_L)	 217℃ 60-150 seconds
Peak Temperature (T_P)	260℃
Time within 5℃ of actual Peak Temperature (t_P)	20-40 seconds
Ramp-down Rate	6℃/second max.
Time 25℃ to Peak Temperature	8 minutes max.


Dimensions (SOIC-08)



Symbol	Dimension			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
A	4.80	5.00	0.189	0.197
B	5.80	6.20	0.228	0.244
C	3.80	4.00	0.150	0.157
D	1.27		0.050	
E	0.33	0.51	0.013	0.020
F	0.40	1.27	0.016	0.050
G	0.19	0.25	0.007	0.010
H	1.35	1.75	0.053	0.069
H1	0.10	0.25	0.004	0.010
H2	1.45		0.057	


Packaging

Tape



Symbol	Dimension (mm)
W	12.00±0.30
P0	4.00±0.10
P1	8.00±0.10
P2	2.00±0.10
D0	Φ1.55±0.10
D1	Φ1.55±0.05
E	1.75±0.10
F	5.50±0.10
A	6.50±0.10
B	5.40±0.10
K	2.00±0.10
t	0.30±0.05

Reel



D	Φ330.0±3.0
D2	Φ13.0
W1	13.5

Quantity: 2500PCS

LEGAL DISCLAIMER

YAGEO, its distributors and agents (collectively, "YAGEO"), hereby disclaims any and all liabilities for any errors, inaccuracies or incompleteness contained in any product related information, including but not limited to product specifications, datasheets, pictures and/or graphics. YAGEO may make changes, modifications and/or improvements to product related information at any time and without notice.

YAGEO makes no representation, warranty, and/or guarantee about the fitness of its products for any particular purpose or the continuing production of any of its products. To the maximum extent permitted by law, YAGEO disclaims (i) any and all liability arising out of the application or use of any YAGEO product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for a particular purpose, non -infringement and merchantability.

YAGEO products are designed for general purpose applications under normal operation and usage conditions. Please contact YAGEO for the applications listed below which require especially high reliability for the prevention of defects which might directly cause damage to the third party's life, body or property: Aerospace equipment (artificial satellite, rocket, etc.), Atomic energy-related equipment, Aviation equipment, Disaster prevention equipment, crime prevention equipment, Electric heating apparatus, burning equipment, Highly public information network equipment, data-processing equipment , Medical devices, Military equipment, Power generation control equipment, Safety equipment, Traffic signal equipment, Transportation equipment and Undersea equipment, or for any other application or use in which the failure of YAGEO products could result in personal injury or death, or serious property damage. Particularly **YAGEO Corporation and its affiliates do not recommend the use of commercial or automotive grade products for high reliability applications or manned space flight.**

Information provided here is intended to indicate product specifications only. YAGEO reserves all the rights for revising this content without further notification, as long as products are unchanged. Any product change will be announced by PCN.