

Power Inductor



BPSF Series



Overview

Power inductors are passive electronic components used in various circuits to store energy in a magnetic field when electrical current flows through them. They are critical in filtering, energy storage, and noise suppression in power electronic systems. They are designed to handle higher currents and are optimized for minimal power loss and thermal efficiency.

Benefits

1. Ferrite SMD Shielded Type
2. Various package size and wide inductance range

Applications

1. AP Routers, STBs
2. LCD TVs and monitors
3. Game consoles
4. LED lights
5. DC/DC converters

Product Information


Series	L (mm)	W(mm)	T (mm)	Inductance (μH)
BPSF	6.0	6.0	2.8	1.2~1500
	7.0	7.0	2.8	
	7.0	7.0	3.0	
	7.0	7.0	3.2	
	7.0	7.0	4.5	
	7.0	7.0	5.5	
	10.1	10.1	4.5	
	10.1	10.1	5.8	
	12.5	12.5	5.5	
	12.5	12.5	6.5	
	12.5	12.5	7.5	



BPSF00131365 Series Specification

1 Scope: This specification applies to SMD Shielded Power Inductors

2 Part Numbering:




3 Rating:

Operating Temperature: - 40°C ~ + 125°C (Including self temp. rise)

Storage Temperature: - 40°C ~ + 125°C (For after the circuit board is mounted)

Storage Temperature: (on tape & reel): -20°C to +40°C; 75% RH max.

4 Marking:



EX:Marking:100

Marking Color:Black


5 Standard Testing Condition

	Unless otherwise specified	In case of doubt
Temperature	Ordinary Temperature(15 to 35°C)	20 to 30°C
Humidity	Ordinary Humidity(25 to 85% RH)	50 to 80 %RH

BPSF00131365 Series Specification

6 Configuration and Dimensions and Unit Weight:

Dimensions in mm



TYPE	131365
A	12.5±0.3
B	12.5±0.3
C	6.5±0.35
D	8.5 typ
E	2.0 typ
F	3.0 typ

Size Code	Net weight(grams)
131365	3.2 (typ.)

7 Electrical Characteristics:

Part No.	Inductance (uH)	Test Freq.	RDC (Ω)	Isat (A)	Irms (A)Max.	Tolerance (±%)	Marking
BPSF001313652R0T00	2	0.5V 1kHz	0.0117±20%	10	6.2	30	2R0
BPSF001313654R2T00	4.2	0.5V 1kHz	0.015±20%	7.3	5.5	30	4R2
BPSF001313657R0T00	7	0.5V 1kHz	0.0177±20%	5.7	5	30	7R0
BPSF00131365100□00	10	0.5V 1kHz	0.0202±20%	5	4.8	20	100
BPSF00131365150□00	15	0.5V 1kHz	0.0237±20%	4.2	4.4	20	150
BPSF00131365220□00	22	0.5V 1kHz	0.0316±20%	3.5	3.8	20	220
BPSF00131365330□00	33	0.5V 1kHz	0.049±20%	2.8	3.4	20	330
BPSF00131365470□00	47	0.5V 1kHz	0.0578±20%	2.4	2.8	20	470
BPSF00131365680□00	68	0.5V 1kHz	0.0787±20%	2	2.4	20	680
BPSF00131365101□00	100	0.5V 1kHz	0.123±20%	1.6	1.9	20	101
BPSF00131365151□00	150	0.5V 1kHz	0.210±20%	1.2	1.5	20	151
BPSF00131365221□00	220	0.5V 1kHz	0.273±20%	1	1.2	20	221


NOTE: □-tolerance M=±20% / T=±30%

1. Operating temperature range -40°C ~ +125°C (Including self temp. rise)
2. Isat for Inductance drop 10% from its value without current.
3. I rms for a 40°C temperature rise from 25°C ambient.

BPSF00131365 Series Specification

8 BPSF00131365 Series

8.1 Construction:



8.2 Material List:

NO.	Part	Material
1	CORE	FERRITE
2	WIRE	MAGNET WIRE
3	BASE	LCP
4	TERMINAL	
5	EPOXY	

BPSF00131365 Series Specification

9 Reliability Of Ferrite Wire Wound Power Inductor


1-1.Mechanical Performance

No	Item	Specification	Test Method
1-1-1	Vibration	Appearance: No damage Inductance: within $\pm 10\%$ of initial value	Test device shall be soldered on the substrate Oscillation Frequency: 10 to 55 to 10Hz for 1min Amplitude: 1.5mm Time: 2hrs for each axis (X, Y & Z), total 6hrs
1-1-2	Resistance to Soldering Heat	Appearance: No damage	Pre-heating: 150°C, 1min Solder Composition: Sn/Ag3.0/Cu0.5 Solder Temperature: 260 ± 5 °C Immersion Time: 10 ± 1 sec
1-1-3	Solder ability	The electrodes shall be at least 95% covered with new solder coating	Pre-heating: 150°C, 1min Solder Composition: Sn/Ag3.0/Cu0.5 Solder Temperature: 245 ± 5 °C Immersion Time: 4 ± 1 sec
1-1-4	Resistance to solvent	There must be no change in appearance or obliteration of marking.	Inductors must withstand 6 minutes of alcohol or water.

1-2.Environmental Performance

1-2 Environmental Performance																		
No	Item	Specification	Test Method															
1-2-1	Temperature Shock	Appearance: No damage Inductance: within $\pm 10\%$ of initial value	10 cycles (Air to Air) 1 cycles shall consist of: 30 minutes exposure to $-55\text{ }^{\circ}\text{C}$ 30 minutes exposure to $125\text{ }^{\circ}\text{C}$ 15 seconds maximum transition between temperatures															
1-2-2	Temperature Cycle		One cycle: <table><tr><th>Step</th><th>Temperature ($^{\circ}\text{C}$)</th><th>Time (min)</th></tr><tr><td>1</td><td>-40 ± 3</td><td>30</td></tr><tr><td>2</td><td>25 ± 2</td><td>3</td></tr><tr><td>3</td><td>125 ± 3</td><td>30</td></tr><tr><td>4</td><td>25 ± 2</td><td>3</td></tr></table>	Step	Temperature ($^{\circ}\text{C}$)	Time (min)	1	-40 ± 3	30	2	25 ± 2	3	3	125 ± 3	30	4	25 ± 2	3
Step	Temperature ($^{\circ}\text{C}$)		Time (min)															
1	-40 ± 3		30															
2	25 ± 2		3															
3	125 ± 3	30																
4	25 ± 2	3																
1-2-3	Humidity Resistance	Total: 100cycles Measured after exposure in the room condition for 24hrs Temperature: $40\pm 2^{\circ}\text{C}$ Relative Humidity: 90 ~ 95% Time: 1000hrs Measured after exposure in the room condition for 24hrs																
1-2-4	Heat Life	Temperature: $85\pm 3^{\circ}\text{C}$ Applied Current: Rated Current Time: 1000hrs Measured after exposure in the room condition for 24hrs																
1-2-5	Cold Resistance	Temperature: $-40\pm 3^{\circ}\text{C}$ Time: 1000hrs Measured after exposure in the room condition for 24hrs																

BPSF00131365 Series Specification



Lead-Free(LF)標準溫度分析範圍

Refer to J-STD-020C

管制項目 Item.	升溫區 Ramp-up	預熱區 Pre-heating	迴焊區 Reflow	Peak Temp	冷卻區 Cooling
溫度範圍 Temp.scope	R.T~150°C	150°C~200°C	Above 217°C	260±5°C	Peak Temp.~150°C
標準時間 Time spec.	—	60~180 sec	60~150 sec	20~40 sec	—
實際時間 Time result	—	75~100 sec	90~120 sec	20~35 sec	—

NOTE:


- 1.Re-flow possible times : within 3 times
- 2.Nitrogen adopted is recommended while in re-flow
- 3.Products can only be soldered with reflow

BPSF00131365 Series Specification

10 Packaging:

10.1 Packaging -Cover Tape


The force for tearing off cover tape is 10 to 130 grams in the arrow direction.



10.2 Packaging Quantity

TYPE	PCS/REEL
131365	500

10.3 Reel Dimensions




Dimensions in mm

TYPE	A	B	C	D
131365	330	100	13	24.4

BPSF00131365 Series Specification


10 Packaging:

10.4 Tape Dimensions in mm



TYPE	A0	B0	K0	D	E	W	P	P0	P2
131365	12.75	12.75	7.0	1.55	1.75	24	16	4	2

11 Recommended Land Pattern:



Dimensions in mm

TYPE	A	B	C	D
131365	3.2	2.6	8.5	2.6



12 Note:

1. Please make sure that your product has been evaluated and confirmed against your specifications when our product is mounted to your product.
2. Do not knock nor drop.
3. All the items and parameters in this product specification have been prescribed on the premise that our product is used for the purpose, under the condition and in the environment agreed upon between you and us. You are requested not to use our product deviating from such agreement.
4. Please keep the distance between transformer/coil and other components (refer to the standard IEC 62368-1)
5. The moisture sensitivity level (MSL) of products is classified as level 1.



BPSF00131365 Series Specification

13 Graph:



BPSF001313652R0T00





BPSF001313654R2T00



BPSF001313657R0T00





BPSF00131365100□00





BPSF00131365 Series Specification

13 Graph:



BPSF00131365150□00




BPSF00131365220□00



BPSF00131365330□00





BPSF00131365470□00





BPSF00131365 Series Specification

13 Graph:



BPSF00131365680□00



BPSF00131365101□00



BPSF00131365151□00



BPSF00131365221□00

