



Note: '()' correspond to the letters used in the product bulletin

**General Information**

Series	SMW/F126
Dielectric	Metallized PPS
Style	SMD Chip
Features	High Stability
RoHS	Yes

**Dimensions**

L	7.3mm +/-0.4mm
W	6mm +/-0.4mm
T	2mm MAX
F	0.5mm NOM

**Packaging Specifications**

Packaging	T&R
Packaging Quantity	3100

**Specifications**

Capacitance	6,800 pF
Tolerance	10%
Voltage DC	100 VDC
Voltage AC	63 VAC
Temperature Range	-55/ +125°C
Rated Temperature	125°C
Dissipation Factor	0.15% 1kHz, 0.25% 10kHz, 0.5% 100kHz
Insulation Resistance	15 GOhms
Max dV/dt	20 V/us

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.