Sample Kit Contents


Part Number	Size	TC	Capacitance	Voltage	Tolerance	Quantity
CC0100JRNPO7BN330	01005	NPO	33pF	16V	±5%	80
CC0100JRNPO7BN101	01005	NPO	100pF	16V	±5%	80
CC0100KRX5R5BB102	01005	X5R	1nF	6.3V	±10%	80
CC0100KRX5R5BB103	01005	X5R	10nF	6.3V	±10%	80
CC0100MRX5R5BB104	01005	X5R	100nF	6.3V	±20%	80
CC0201CRNPO9BNR50	0201	NPO	0.5pF	50V	±0.25pF	80
CC0201CRNPO9BN1R0	0201	NPO	1pF	50V	±0.25pF	80
CC0201CRNPO9BN1R5	0201	NPO	1.5pF	50V	±0.25pF	80
CC0201CRNPO9BN2R2	0201	NPO	2.2pF	50V	±0.25pF	80
CC0201CRNPO9BN2R7	0201	NPO	2.7pF	50V	±0.25pF	80
CC0201CRNPO9BN3R3	0201	NPO	3.3pF	50V	±0.25pF	80
CC0201CRNPO9BN3R9	0201	NPO	3.9pF	50V	±0.25pF	80
CC0201CRNPO9BN4R7	0201	NPO	4.7pF	50V	±0.25pF	80
CC0201CRNPO9BN5R6	0201	NPO	5.6pF	50V	±0.25pF	80
CC0201CRNPO9BN6R0	0201	NPO	6pF	50V	±0.25pF	80
CC0201CRNPO9BN6R8	0201	NPO	6.8pF	50V	±0.25pF	80
CC0201CRNPO9BN8R2	0201	NPO	8.2pF	50V	±0.25pF	80
CC0201JRNPO9BN100	0201	NPO	10pF	50V	±5%	80
CC0201JRNPO9BN150	0201	NPO	15pF	50V	±5%	80
CC0201JRNPO9BN180	0201	NPO	18pF	50V	±5%	80
CC0201JRNPO9BN220	0201	NPO	22pF	50V	±5%	80
CC0201JRNPO9BN330	0201	NPO	33pF	50V	±5%	80
CC0201JRNPO9BN390	0201	NPO	39pF	50V	±5%	80
CC0201JRNPO9BN470	0201	NPO	47pF	50V	±5%	80
CC0201JRNPO9BN560	0201	NPO	56pF	50V	±5%	80
Part Number	**Size**	**TC**	**Capacitance**	**Voltage**	**Tolerance**	**Quantity**


Sample Kit Contents cont.

Part Number	Size	TC	Capacitance	Voltage	Tolerance	Quantity
CC0201JRNPO9BN680	0201	NPO	68pF	50V	±5%	80
CC0201JRNPO9BN820	0201	NPO	82pF	50V	±5%	80
CC0201JRNPO9BN101	0201	NPO	100pF	50V	±5%	80
CC0201KRX7R6BB472	0201	X7R	4.7nF	10V	±10%	80
CC0201KRX7R6BB682	0201	X7R	6.8nF	10V	±10%	80
CC0201KRX7R7BB222	0201	X7R	2.2nF	16V	±10%	80
CC0201KRX7R7BB332	0201	X7R	3.3nF	16V	±10%	80
CC0201KRX7R7BB103	0201	X7R	10nF	16V	±10%	80
CC0201KRX7R8BB681	0201	X7R	680pF	25V	±10%	80
CC0201KRX7R8BB102	0201	X7R	1nF	25V	±10%	80
CC0201KRX7R9BB221	0201	X7R	220pF	50V	±10%	80
CC0201KRX7R9BB471	0201	X7R	470pF	50V	±10%	80
CC0201KRX7R9BB102	0201	X7R	1nF	50V	±10%	80
CC0201KRX6S5BB104	0201	X6S	100nF	6.3V	±10%	80
CC0201KRX5R5BB223	0201	X5R	22nF	6.3V	±10%	80
CC0201KRX5R5BB333	0201	X5R	33nF	6.3V	±10%	80
CC0201KRX5R5BB473	0201	X5R	47nF	6.3V	±10%	80
CC0201KRX5R5BB104	0201	X5R	100nF	6.3V	±10%	80
CC0201MRX5R5BB224	0201	X5R	220nF	6.3V	±20%	80
CC0201MRX5R5BB474	0201	X5R	470nF	6.3V	±20%	80
CC0201MRX5R5BB105	0201	X5R	1uF	6.3V	±20%	80
CC0201MRX5R5BB225	0201	X5R	2.2uF	6.3V	±20%	80
CC0201KRX5R6BB104	0201	X5R	100nF	10V	±10%	80
CC0201MRX5R6BB224	0201	X5R	220nF	10V	±20%	80
CC0201KRX5R8BB103	0201	X5R	10nF	25V	±10%	80
Part Number	**Size**	**TC**	**Capacitance**	**Voltage**	**Tolerance**	**Quantity**

Scope

This product specification is applied to Multi-layer Ceramic Capacitor used for Automotive application .





Revision History

Revision	Date	Change notification	Description
Version 0	Nov, 02, 2026	-	- New datasheet, Engineering Kit for SS1111000000SB000 CC Small Size series.