Innovative Service Around the Globe YAGEO

DATA SHEET

METAL OXIDE VARISTORS
POWER SUPPLY

07H series

RoHS compliant & Halogen free




Product specification– May 21, 2026 V.6

Metal Oxide Varistors (MOV) Data Sheet

Features


- Wide operating voltage (V_{1mA}) range from 82V to 820V
- Fast responding to transient over-voltage
- Large absorbing transient energy capability
- Low clamping ratio and no follow-on current
- Meets MSL level 1, per J-STD-020
- Operating Temperature：-40℃ ~ +140℃
- Storage Temperature：-40℃ ~ +140℃
- Safety certification: UL: E327997
  TUV: B0960480010
  CQC:17001172542
  CSA: 246579




Applications

- Transistor, diode, IC, thyristor or triac semiconductor protection
- Surge protection in consumer electronics
- Surge protection in industrial electronics
- Surge protection in electronic home appliances, gas and petroleum appliances
- Relay and electromagnetic valve surge absorption

Part Number Code



Dimensions



O TYPE

Table 1

Unit: mm

Symbol	Dimension
H	7.5~13.0
H1	9.0~13.5
L(min.)	20.0
L1(min.)	15.0
D	7.0~10.0
F(±0.8)	5.0
T	Table 2
e(±0.8)	Table 2
d(±0.05)	0.6
d1(±0.4)	1.2

Table 2

Unit: mm

Model	T	e	Model	T	e
820K	2.18~4.89	1.4	391K	2.95~6.42	2.6
101K	2.28~5.06	1.6	431K	3.08~6.66	2.8
121K	2.40~5.26	1.7	471K	3.21~6.89	3.0
151K	2.18~4.99	1.8	511K	3.34~7.13	3.2
181K	2.28~5.17	1.7	561K	3.50~7.43	3.4
201K	2.36~5.32	1.8	621K	3.69~7.79	3.7
221K	2.41~5.41	1.9	681K	3.89~8.14	4.0
241K	2.47~5.53	2.0	751K	4.11~8.56	4.1
271K	2.57~5.71	2.2	781K	4.21~8.74	4.2
301K	2.66~5.88	2.3	821K	4.34~8.98	4.4
331K	2.76~6.06	2.3			
361K	2.86~6.24	2.5			


Electrical Characteristics

Part Number		Maximum Allowable Voltage		Varistor Voltage	Maximum Clamping Voltage		Withstanding Surge Current		Maximum Energy (10/1000μs)		Rated Power	Typical Capacitance (Reference)
Standard	High Surge	V_{AC} (V)	V_{DC} (V)	V_{1mA} (V)	I_P (A)	V_C (V)	I (A) Standard	I (A) High Surge	(J) Standard	(J) High Surge	(W)	@1KHz (pf)
820KH07	820KH07J	50	65	82(74~90)	10	135	1200	1750	5.0	10.0	0.25	600
101KH07	101KH07J	60	85	100(90~110)	10	165	1200	1750	6.5	12.0	0.25	500
121KH07	121KH07J	75	100	120(108~132)	10	200	1200	1750	7.8	13.0	0.25	420
151KH07	151KH07J	95	125	150(135~165)	10	250	1200	1750	9.7	15.0	0.25	330
181KH07	181KH07J	115	150	180(162~198)	10	300	1200	1750	11.7	16.0	0.25	280
201KH07	201KH07J	130	170	200(180~220)	10	340	1200	1750	13.0	17.0	0.25	250
221KH07	221KH07J	140	180	220(198~242)	10	360	1200	1750	14.0	19.0	0.25	230
241KH07	241KH07J	150	200	240(216~264)	10	395	1200	1750	15.0	21.0	0.25	210
271KH07	271KH07J	175	225	270(243~297)	10	455	1200	1750	18.0	24.0	0.25	185
301KH07	301KH07J	190	250	300(270~330)	10	500	1200	1750	20.0	26.0	0.25	165
331KH07	331KH07J	210	275	330(297~363)	10	550	1200	1750	23.0	28.0	0.25	150
361KH07	361KH07J	230	300	360(324~396)	10	595	1200	1750	24.0	32.0	0.25	140
391KH07	391KH07J	250	320	390(351~429)	10	650	1200	1750	26.0	35.0	0.25	130
431KH07	431KH07J	275	350	430(387~473)	10	710	1200	1750	28.0	40.0	0.25	115
471KH07	471KH07J	300	385	470(423~517)	10	775	1200	1750	29.0	42.0	0.25	105
511KH07	511KH07J	320	415	510(459~561)	10	845	1200	1750	31.0	45.0	0.25	100
561KH07	561KH07J	350	460	560(504~616)	10	925	1200	1750	35.0	49.0	0.25	90
621KH07	621KH07J	385	505	620(558~682)	10	1025	1200	1750	38.0	55.0	0.25	80
681KH07	681KH07J	420	560	680(612~748)	10	1120	1200	1750	42.0	60.0	0.25	75
751KH07	/	460	615	750(675~825)	10	1240	1200	/	45.0	/	0.25	70
781KH07	/	485	640	780(702~858)	10	1290	1200	/	48.0	/	0.25	65
821KH07	/	510	670	820(738~902)	10	1355	1200	/	52.0	/	0.25	60

Notes: 1.Leakage Current (@83% of V_{1mA})： IR≤20μA (820K~821K)


2.Varistor voltage=750V and 820V do not produce High Surge products

Electrical Ratings

Items	Test Condition/Description	Requirement
Varistor Voltage	The voltage between the two terminals with the specified measuring current 1mA.DC applied is called Vb.	To meet the Specified value
Maximum Allowable Voltage	The recommended maximum sine wave voltage (RMS) or the Maximum DC voltage can be applied continuously.	
Maximum Clamping Voltage	The maximum voltage between the two terminals with the specification standard impulse current. Applied waveform: 8/20μs 	
Rated Wattage	The maximum average power that can be applied within the specified ambient temperature.	
Energy	The maximum energy within the varistor voltage change of ±10% when one impulse of 10/1000μs or 2ms is applied.	
Withstanding Surge Current	The maximum current within the varistor voltage change of ±10% with the standard impulse current (8/20μs) applied one time.	
Varistor Voltage Temp. Coefficient	$\left\lvert \frac{V_{1mA@140℃}-V_{1mA@25℃}}{V_{1mA@25℃}} \times \frac{1}{115} \times 100\%(\%/℃) \right\rvert$	≤0.05%/℃
	$\left\lvert \frac{V_{1mA@-40℃}-V_{1mA@25℃}}{V_{1mA@25℃}} \times \frac{1}{65} \times 100\%(\%/℃) \right\rvert$	
Surge Life	The change of Vb shall be measured after the impulse listed below which is applied 10,000 times continuously with the interval of ten seconds at room temperature. 7Φ series | 820K to 821K | 50A (8/20μs)	$\frac{\Delta Vb}{Vb} \leq \pm 10\%$

Soldering Recommendation

Lead-free Wave Soldering Recommendation



Item	Conditions
Peak Temperature	265℃
Dipping Time	10 seconds (max.)
Soldering	1 time

Recommendation Reworking Conditions with Soldering Iron

Item	Conditions
Temperature of Soldering Iron-tip	360℃ (max.)
Soldering Time	3 seconds (max.)
Distance from Varistor	2mm (min.)


Mechanical Characteristics

Items	Test conditions / Methods	Specifications
Tensile Strength of Terminals	Gradually applying the force specified and keeping the unit fixed for 10±1 sec. Terminal diameter (mm) / Force (kg) 0.5＜d≤0.8 / 1.0 0.8＜d≤1.25 / 2.0 1.25＜d / 4.0	No visible damage $\|\Delta V_{1mA}/V_{1mA}\| \leq 5\%$
Bending Strength of Terminals	Hold specimen and apply the force specified below to each lead. Bend the specimen to 90°, then return to the original position. Repeat the procedure in the opposite direction. Terminal diameter (mm) / Force (kg) 0.5＜d≤0.8 / 0.5 0.8＜d≤1.25 / 1.0 1.25＜d / 2.0	No visible damage $\|\Delta V_{1mA}/V_{1mA}\| \leq 5\%$
Vibration	Frequency range: 10~55 Hz Amplitude: 0.75mm or 98m/s^2 Direction: 3 mutually perpendicular directions, 2hrs each.	No visible damage $\|\Delta V_{1mA}/V_{1mA}\| \leq 5\%$
Solder ability	Solder Temp: 245±5℃ Dipping Time: 2±0.5 sec	At least 95% of terminal electrode is covered by new solder
Resistance to Soldering Heat	Solder Temp: 260±5℃ Dipping Time: 10±1 sec	No visible damage $\|\Delta V_{1mA}/V_{1mA}\| \leq 10\%$


Reliability


Items	Test conditions / Methods	Specifications
High Temperature Storage	Ambient Temp: 140±2℃ Duration: 1000hrs	$\|\Delta V_{1mA}/V_{1mA}\| \leq 5\%$
Low Temperature Storage	Ambient Temp: -40±2℃ Duration: 1000hrs	$\|\Delta V_{1mA}/V_{1mA}\| \leq 5\%$
Humidity	Ambient Temp: 40±2℃, 90~95% R.H. Duration: 1000hrs	$\|\Delta V_{1mA}/V_{1mA}\| \leq 5\%$
Temperature Cycle	The conditions shown below shall be repeated 5 cycles Step / Temperature (℃) / Period (minutes) 1 / -40±3 / 30±3 2 / Room temperature / 15±3 3 / 140±3 / 30±3 4 / Room temperature / 15±3	No visible damage $\|\Delta V_{1mA}/V_{1mA}\| \leq 5\%$
High Temperature Load	Ambient Temp: 140±2℃ Duration: 1000hrs Load: Max. Allowable Voltage In AC eara.	$\|\Delta V_{1mA}/V_{1mA}\| \leq 10\%$
Damp Heat Load	Ambient Temp: 40±2℃, 90~95% R.H. Duration: 1000hrs Load: Max. Allowable Voltage	No visible damage $\|\Delta V_{1mA}/V_{1mA}\| \leq 10\%$
Voltage Proof	Metal balls method, 1000Vac 1 min.(820K~331K), 1500Vac 1 min.(361K~821K)	No visible damage

Power Derating Curve





Maximum Surge Current Derating Curve







Maximum Leakage Current and Maximum Clamping Voltage Curve







820KH07J to 471KH07J
10000
1000
100
10
Voltage (V)
Maximum Clamping Voltage
Maximum Leakage Current
471KH07J
431KH07J
391KH07J
361KH07J
331KH07J
301KH07J
271KH07J
241KH07J
221KH07J
201KH07J
181KH07J
151KH07J
121KH07J
101KH07J
820KH07J
10-6
10-5
10-4
10-3
10-2
10-1
1
10
102
103
104
105
Current (A)



511KH07J to 681KH07J
10000
1000
100
Voltage (V)
Maximum Clamping Voltage
Maximum Leakage Current
681KH07J
621KH07J
561KH07J
511KH07J
10-6
10-5
10-4
10-3
10-2
10-1
1
10
102
103
104
105
Current (A)

Marking Code



① Brightking Logo
② Varistor Voltage
③ “J” is High Surge Code, no “J” is Standard Surge
④ Varistor Size

Quantity

Packaging Dimensions (Unit: mm)	Quantity
Bulk 	1000pcs/bag 2bags/box (820K~391K)
	800pcs/bag 2bags/box (431K~621K)
	600pcs/bag 2bags/box (681K~821K)

Legal Disclaimer

YAGEO, its distributors and agents (collectively, "YAGEO"), hereby disclaims any and all liabilities for any errors, inaccuracies or incompleteness contained in any product related information, including but not limited to product specifications, datasheets, pictures and/or graphics. YAGEO may make changes, modifications and/or improvements to product related information at any time and without notice.

YAGEO makes no representation, warranty, and/or guarantee about the fitness of its products for any particular purpose or the continuing production of any of its products. To the maximum extent permitted by law, YAGEO disclaims (i) any and all liability arising out of the application or use of any YAGEO product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for a particular purpose, non -infringement and merchantability.

YAGEO products are designed for general purpose applications under normal operation and usage conditions. Please contact YAGEO for the applications listed below which require especially high reliability for the prevention of defects which might directly cause damage to the third party's life, body or property: Aerospace equipment (artificial satellite, rocket, etc.), Atomic energy-related equipment, Aviation equipment, Disaster prevention equipment, crime prevention equipment, Electric heating apparatus, burning equipment, Highly public information network equipment, data-processing equipment , Medical devices, Military equipment, Power generation control equipment, Safety equipment, Traffic signal equipment, Transportation equipment and Undersea equipment, or for any other application or use in which the failure of YAGEO products could result in personal injury or death, or serious property damage. Particularly **YAGEO Corporation and its affiliates do not recommend the use of commercial or automotive grade products for high reliability applications or manned space flight.**

Information provided here is intended to indicate product specifications only. YAGEO reserves all the rights for revising this content without further notification, as long as products are unchanged. Any product change will be announced by PCN.