Innovative Service Around the Globe YAGEO


DATA SHEET

ELECTROSTATIC DISCHARGE PROTECTION DEVICES

INDUSTRIAL / CONSUMER

SZD30A15L01

RoHS compliant & Halogen free





Product specification– July 02, 2023 V.1

Electrostatic Discharged Protection Devices (ESD) Data Sheet

Description

The SZD22A30L01 is designed to protect voltage sensitive components from ESD and transient voltage events. protect power port and the chip Vbus interfaces. It has been specifically designed to protect sensitive components which are connected to power lines from overvoltage caused by electrostatic discharge (ESD),cable discharge events (CDE) and lightning.

The device integrate a high power transient voltage suppressor(TVS) and small package. It features solid-state silicon-avalanche technology for unmatched transient protection without device degradation. It offer superior electrical characteristics including fast response time, low clamping voltage and no device degradation. This allows the designer maximum flexibility and reduces parts count.

The device may be used to meet the immunity requirements of IEC61000-4-2 (ESD), IEC61000-4-4 (EFT) , IEC61000-4-5 (Surge)




Contact : ±30kV
Air : ±30kV



Features

- IEC61000-4-2 ESD 30KV Air, 30KV contact compliance
- DFN2020 surface mount package
- Working voltage: 30V
- Low leakage current
- Low operating and clamping voltages
- Lead Free/RoHS compliant
- Flammability rating UL 94V-0
- Meets MSL level 1, per J-STD-020
- Marking: P30 004



Pin Configuration

Applications

- Power port
- I^2C bus protection

Maximum Ratings

Rating	Symbol	Value	Unit
Peak pulse power (tp=8/20μs waveform)	Ppp	9000	W
ESD voltage (Contact discharge)	V_{ESD}	±30	kV
ESD voltage (Air discharge)		±30	
Storage & operating temperature range	T_{STG} ,T_J	-55~+150	℃

Electrical Characteristics (T_J=25℃)

Parameter	Symbol	Condition	Min.	Typ.	Max.	Unit
Reverse stand-off voltage	V_{RWM}				30	V
Reverse breakdown voltage	V_{BR}	I_{BR}=1.0mA	31			V
Reverse leakage current	I_R	V_R=30V			1.0	μA
Clamping voltage (tp=8/20μs)	V_C	I_{PP}=180A		50	70	V
Peak Pulse Current(tp=8/20μs)	I_{PP}				180	A
ESD Clamping voltage (TLP)	V_C	I_{PP}=8.0A		33		V
ESD Clamping voltage (TLP)	V_C	I_{PP}=16A		34		V
ESD Dynamic Turn-on Resistance	R_{dy}			0.12		Ω
Off state junction capacitance	C_J	0Vdc,f=1MHz		570	670	pF

Typical Characteristics Curves

Figure 1. Pulse Waveforms




Figure 2. Clamping Voltage vs. Peak Pulse Current




Figure 3. Capacitance vs. Reverse Voltage






Figure 4.Transmission LinePulsing (TLP) Measurement



Recommended Soldering Conditions


Reflow Soldering



Recommended Conditions

Profile Feature	Pb-Free Assembly
Average ramp-up rate (T_L to T_P)	3℃/second max.
Preheat -Temperature Min ($T_{S\ min}$) -Temperature Max ($T_{S\ max}$) -Time (min to max) (t_S)	 150℃ 200℃ 60-180 seconds
$T_{S\ max}$ to T_L -Ramp-up Rate	 3℃/second max.
Time maintained above: -Temperature (T_L) -Time (t_L)	 217℃ 60-150 seconds
Peak Temperature (T_P)	260℃
Time within 5℃ of actual Peak Temperature (t_P)	20-40 seconds
Ramp-down Rate	6℃/second max.
Time 25℃ to Peak Temperature	8 minutes max.


Dimensions (DFN2020)



Symbol	Dimension			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
A	0.50	0.60	0.020	0.024
D	1.90	2.10	0.075	0.083
D1	1.40	1.60	0.055	0.063
E	1.90	2.10	0.075	0.083
E1	0.90	1.15	0.035	0.045
e	1.30 BSC		0.051 BSC	
L1	0.324	0.476	0.013	0.019
L2	0.20	0.30	0.008	0.012
k	0.20	0.45	0.008	0.018
h	0.30 BSC		0.012 BSC	


Packaging

Tape



Symbol	Dimension (mm)
W	8.00±0.30
P0	4.00±0.10
P1	4.00±0.10
P2	2.00±0.10
D0	Φ1.50±0.10
E	1.75±0.10
F	3.50±0.10
A0	2.25±0.1
B0	2.25±0.1

Reel



D	Φ178.0±2.0
D2	Φ54.50±1
W1	9.5±2
W2	Φ12.30±1.5
Quantity: 3000PCS	

LEGAL DISCLAIMER

YAGEO, its distributors and agents (collectively, "YAGEO"), hereby disclaims any and all liabilities for any errors, inaccuracies or incompleteness contained in any product related information, including but not limited to product specifications, datasheets, pictures and/or graphics. YAGEO may make changes, modifications and/or improvements to product related information at any time and without notice.

YAGEO makes no representation, warranty, and/or guarantee about the fitness of its products for any particular purpose or the continuing production of any of its products. To the maximum extent permitted by law, YAGEO disclaims (i) any and all liability arising out of the application or use of any YAGEO product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for a particular purpose, non -infringement and merchantability.

YAGEO products are designed for general purpose applications under normal operation and usage conditions. Please contact YAGEO for the applications listed below which require especially high reliability for the prevention of defects which might directly cause damage to the third party's life, body or property: Aerospace equipment (artificial satellite, rocket, etc.), Atomic energy-related equipment, Aviation equipment, Disaster prevention equipment, crime prevention equipment, Electric heating apparatus, burning equipment, Highly public information network equipment, data-processing equipment , Medical devices, Military equipment, Power generation control equipment, Safety equipment, Traffic signal equipment, Transportation equipment and Undersea equipment, or for any other application or use in which the failure of YAGEO products could result in personal injury or death, or serious property damage. Particularly **YAGEO Corporation and its affiliates do not recommend the use of commercial or automotive grade products for high reliability applications or manned space flight.**

Information provided here is intended to indicate product specifications only. YAGEO reserves all the rights for revising this content without further notification, as long as products are unchanged. Any product change will be announced by PCN.