



Click [here](#) for the 3D model.

**General Information**

Series	SMD Mil-Equiv X7R HV 49467
Style	SMD Chip
Description	Surface Mount Ceramic Capacitor
RoHS	No
Prop 65	<b>WARNING:</b> Cancer and reproductive harm - <a href="https://www.p65warnings.ca.gov/">https://www.p65warnings.ca.gov/</a>
SCIP Number	a9ede7c3-8ff0-4777-aadd-7850aa043418
Termination	Silver Nickel Tin Lead (SnPb)

**Dimensions**

L	4.57mm +/-0.51mm
W	3.05mm +/-0.38mm
T	2.54mm NOM
B	0.64mm +/-0.38mm
Case Code (EIA / mm)	1812 / 4532

**Packaging Specifications**

Packaging	Waffle, Tray
Packaging Quantity	50

**Specifications**

Capacitance	0.01 uF
Tolerance	10%
Voltage DC	1000 VDC
Dielectric Withstanding Voltage	1,200 VDC
Temperature Range	-55/+125°C
Temp. Coefficient	X7R
Capacitance Change with Reference to +25°C and 0 VDC Applied (TCC)	30 ppm/C
Dissipation Factor	2.5% 1 kHz 1.0Vrms
Aging Rate	2% Loss/Decade Hour
Insulation Resistance	100 GOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.