

2x2 MiMo 5dBi WiFi Antenna SMA-Male Connector

LPTNG2471M2DMG0457: 2400-2500 and 4900-7125MHz



Features & Applications:

- 2x2 MiMo WiFi6E/7
- Ground independent (w/ mounting washer)
- UL94-V0 Fire Rating
- Low profile 34.3mm when installed
- Indoor and outdoor use IP67 / UV rated
- IoT, M2M, industrial metering
- DSRC, ISM band radios

Electrical specifications @ 25° C – Operating Temperatures – 40°C to +80°C							
Frequency Bands – 2400-2500MHz & 4900-7125MHz							
Antenna type	Nominal Impedance	Polarization		Radiation pattern		Power withstanding	DC Ground
Dipole	50Ω	Linear		Omni		3W	No
	Mounting surface	Free Space ⁴		Dia 120mm GP test		Dia 300mm GP test	
	Frequency (MHz)	2400-2500	4900-7125	2400-2500	4900-7125	2400-2500	4900-7125
Port 1	VSWR	< 2	< 2.5	< 2	< 2.5	< 2	< 2.5
	Return Loss (dB)	< -10	< -7.5	< -10	< -7.5	< -10	< -7.5
	Avg. Peak Gain (dBi)	4.5	3.0	4.1	5.1	2.1	4.9
	Avg. Efficiency (%)	69	66	69	67	65	68
Port 2	VSWR	< 2	< 2.5	< 2	< 2.5	< 2	< 2.5
	Return Loss (dB)	< -10	< -7.5	< -10	< -7.5	< -10	< -7.5
	Avg. Peak Gain (dBi)	5.9	3.6	3.9	5.6	3.8	5.7
	Avg. Efficiency (%)	68	65	68	66	68	67

Mechanical Specifications				
Orderable P/N: LPTNG2471M2DMG0457				
Size (Diameter x Height)	Weight	Housing Color	Housing Material	Fixing System
Φ45.50 X 53.5 mm (Φ1.79x2.11")	185 g	Black	PC (UV-stabilized)	Direct Mount
Height installed	Connector Type	Cable Style	Cable Length	
34.3 mm / 1.35" (After compression)	SMA-Male	RG316 or equivalent	457mm (1.5FT)	

Environmental Specifications				
Operating Temperature	Storage Temperature	Ingress Protection	Flame Rating	RoHS Compliant
-40°C to 85°C	-40°C to 85°C	IP67	UL94-V0	Yes

Notes:

1. Flame Rating (radome): UL94-V0.
2. Operating temp and Storage temp to be -40°C ~ 85°C.
3. Physical: Dimensional stability, Value to be 0.0%, Test method to be ASTM D1042 ISO2796.
4. Specifications measured with supplied Dia 60mm Mounting Washer.

2x2 MiMo 5dBi WiFi Antenna SMA-Male Connector

LPTNG2471M2DMG0457: 2400-2500 and 4900-7125MHz


Family Products – LPT WiFi

LPT WiFi 6E/7 Products 2400-2500/4900-7125MHZ

Orderable P/N	No. of Total Ports	Siso/MiMo	Cable length	Connector	Ground Independent	Note
LPT2400/71DMN	1	Siso	No	N-Female	No	
LPTNG2400/71DMN	1	Siso	No	N-Female	Yes	
LPTNG24-71DMG0457	1	Siso	457mm(1.5Ft)	SMA-Male	Yes	
LPTNG2471M2DMG0457	2	2xMiMo	457mm(1.5Ft)	SMA-Male	Yes	

Mechanical Drawing

LPTNG2471M2DMG0457




Dimensions: [mm] Inches

2x2 MiMo 5dBi WiFi Antenna SMA-Male Connector


LPTNG2471M2DMG0457: 2400-2500 and 4900-7125MHz

Testing Setup


LPTNG2471M2DMG0457



Radiation element is test on D60mm ground plane
(D60mm flat washer is standard part in the packing)



Radiation element is test on D120mm ground plane






Radiation element is test on D300mm ground plane

2x2 MiMo 5dBi WiFi Antenna SMA-Male Connector

LPTNG2471M2DMG0457: 2400-2500 and 4900-7125MHz

Charts- VSWR , Return Loss and Isolation




LPTNG2471M2DMG0457



Antenna test with 1.5FT RG316 cable & SMA connector

2x2 MiMo 5dBi WiFi Antenna SMA-Male Connector




LPTNG2471M2DMG0457: 2400-2500 and 4900-7125MHz



Antenna test with 1.5FT RG316 cable & SMA connector

2x2 MiMo 5dBi WiFi Antenna SMA-Male Connector

LPTNG2471M2DMG0457: 2400-2500 and 4900-7125MHz






Antenna test with 1.5FT RG316 cable & SMA connector

2x2 MiMo 5dBi WiFi Antenna SMA-Male Connector

LPTNG2471M2DMG0457: 2400-2500 and 4900-7125MHz

Charts- Efficiency, and Peak Gain




LPTNG2471M2DMG0457



Antenna test with 1.5FT RG316 cable & SMA connector

2x2 MiMo 5dBi WiFi Antenna SMA-Male Connector

LPTNG2471M2DMG0457: 2400-2500 and 4900-7125MHz




Antenna test with 1.5FT RG316 cable & SMA connector

2x2 MiMo 5dBi WiFi Antenna SMA-Male Connector

LPTNG2471M2DMG0457: 2400-2500 and 4900-7125MHz

Port1_Charts-XY Gain Plots


LPTNG2471M2DMG0457



D60mm


D120mm

D300mm



Port1_Charts – ZX Gain Plots


LPTNG2471M2DMG0457



D60mm

D120mm

D300mm




2x2 MiMo 5dBi WiFi Antenna SMA-Male Connector

LPTNG2471M2DMG0457: 2400-2500 and 4900-7125MHz

Port1_Charts – ZY Gain Plots


LPTNG2471M2DMG0457



D60mm


D120mm

D300mm



Port2_Charts – XY Gain Plots


LPTNG2471M2DMG0457



D60mm

D120mm

D300mm




2x2 MiMo 5dBi WiFi Antenna SMA-Male Connector

LPTNG2471M2DMG0457: 2400-2500 and 4900-7125MHz


Port2_Charts – ZX Gain Plots

LPTNG2471M2DMG0457



Port2_Charts – ZY Gain Plots

LPTNG2471M2DMG0457



Antenna test with 1.5FT RG316 cable & SMA connector

2x2 MiMo 5dBi WiFi Antenna SMA-Male Connector

LPTNG2471M2DMG0457: 2400-2500 and 4900-7125MHz



Packaging

LPTNG2471M2DMG0457

1. Antennas packed in a plastic bag.
2. Label on each plastic bag with part number, description, date code.
3. Out box:400x300x300mm, 48Pcs/Box;

For More Information:

Americas - antennas.us@pulseelectronics.com | Europe – antennas.eu@pulseelectronics.com | Asia – antennas.as@pulseelectronics.com | Questions? +1-800-ANTENNA
Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright , 2020. Pulse Electronics, Inc. All rights reserved.
Company address: Pulse Electronics, a YAGEO Company, 15255 Innovation Drive, Suite #100, San Diego, CA 92128

'YAGEO Corporation and its affiliates do not recommend the use of commercial, automotive, and/or COTS grade products for high reliability applications or manned space flight.'