


# CRF Series Datasheet

Precision Fusible Safety Wirewound Resistors | Axial and SMD Version  
Ceramic core | Flame retardant coating | UL1412 Recognized (file E330640)



## ORDERING CODE - Example

New SAP Part Nr.:

<b>CRF</b>	<b>300</b>	<b>J</b>	<b>T</b>	<b>-</b>	<b>73-</b>	<b>150R</b>	<b>UL</b>
Serie	* Power rating	Tol.	Pack-Code	TCR	Forming type	R Value	Special
		J = ±5%	T = Tape (ammo pack)	- Base on spec.	52- Inner Taping dimension or 73- Inner Taping dimension ZB- Z version		UL = UL Version YY = Standard

Historical VTM Part Nr.:

<b>CRF254 - 8</b>	<b>5</b>	<b>T</b>	<b>150R</b>
Type	Tol.	Pack-Code	R Value

<b>RZS4</b>	<b>6720</b>	<b>J</b>	<b>K</b>	<b>-</b>	<b>13</b>	<b>150R</b>
Type	Size	Tol.	K = Blister tape reel	TC	Reel diam.	R Value

## APPLICATIONS

- Industrial
- Consumer & Electronics
- Power & Energy
- Computer & Peripherals
- Automotive

## FEATURES


- Precision Type
- "Z" preforming ; Other preforming available
- UL approval, file E330640
- 240[V] fusing application
- RoHs Compliant

## ELECTRICAL SPECIFICATIONS


Type			CRF110	CRF200	CRF250	CRF300	CRF400	CRF500
Historical Part Number	AXIAL	Standard	CRF251-4	CRF252-4	CRF253-4	CRF254-4	CRF256-4	CRF257-4
		UL	CRF251-8	CRF252-8	CRF253-8	CRF254-8	CRF256-8	CRF257-8
SMD			RZS1	RZS2	RZS3	RZS4	RZS6	-----
Nominal Power Rating	P <sub>40</sub> *	[W]	1,1	2,0	2,5	3,0	4,0	5,0
	P <sub>70</sub>		1,0	1,8	2,3	2,7	3,6	4,5
Resistance Range		[Ω]	1R ... 100R	1R ... 240R	1R ... 330R	1R ... 470R	1R ... 330R	1R ... 330R
			(Other values upon request, for CRF UL approval check the ohmic value range below page 2)					
E-Series (preferred)			E24 (Other upon request)					
Tolerances		±[%]	J = 5%					
Temperature Coefficient		±[10 <sup>-6</sup> *K <sup>-1</sup> ]	120 ±50					
Working Temperature Range		[°C]	-55 ... +350					
Thermal Resistance		[KW <sup>-1</sup> ]	280	155	122	104	78	62
Max. Working Voltage		[V] <sub>RMS</sub>	$\sqrt{P_{70} \times R}$					
Dielectric Withstanding Voltage IEC115-1 clause 4.7 (1[min])		[V] <sub>RMS</sub>	500					

# CRF Series Datasheet

Precision Fusible Safety Wirewound Resistors | Axial and SMD Version  
Ceramic core | Flame retardant coating | UL1412 Recognized (file E330640)



## DIMENSIONS [mm]



Type	Historical P/N:	L max.	Ø D max.*	Ø d ±0,05
<b>CRF110</b>	CRF251-4 / -8	9,0	3,0	0,65
<b>CRF200</b>	CRF252-4 / -8	9,7	4,0	0,80
<b>CRF250</b>	CRF253-4 / -8	14,5	4,5	0,65
<b>CRF300</b>	CRF254-4 / -8	12,6	6,0	0,80
<b>CRF400</b>	CRF256-4 / -8	17,0	6,0	0,80
<b>CRF500</b>	CRF257-4 / -8	18,0	8,5	0,80


\*R <10R D max.+1

## PERFORMANCE DATA

Type		CRF110	CRF200	CRF250	CRF300	CRF400	CRF500	
Historical Part Number	AXIAL	Standard	CRF251-4	CRF252-4	CRF253-4	CRF254-4	CRF256-4	CRF257-4
		UL	CRF251-8	CRF252-8	CRF253-8	CRF254-8	CRF256-8	CRF257-8
	SMD	RZS1	RZS2	RZS3	RZS4	RZS6	-----	
Derating Linear	[°C]	70...350 (0W)						
Climatic Category		55/350/56						
Failure Rate <i>(Total, <math>\vartheta_o</math>, max, 60[%] cont. lev.)</i>	[10 <sup>-9</sup> h <sup>-1</sup> ]	appr. 10 depends on value						
Endurance <i>IEC60115-1 clause 4.25 (P70, @ 70[°C], 1000[h])</i>	±[%]	5,0						
Damp Heat, Steady State <i>IEC60115-1 clause 4.24 (40[°C], 93[% r.h.], 56[d])</i>	±[%]	5,0						
Climatic Sequence <i>IEC60115-1 clause 4.23 (260±5[°C], 10±1[s])</i>	±[%]	2,0						
Resistance to Soldering <i>Heat IEC60115-1 clause 4.18 (260±5[°C], 10±1[s])</i>	±[%]	1,0						
Terminal Strength	±[%]	0,2						
Terminal Tensile Strength	[N]	40	50					
Solderability <i>IEC60068-2-20 (245±5[°C] 3±0,5[s])</i>		Solder bath method (> 95% coverage)						
Marking <i>IEC60062</i>		Printed in clear						

# CRF Series Datasheet

Precision Fusible Safety Wirewound Resistors | Axial and SMD Version  
Ceramic core | Flame retardant coating | UL1412 Recognized (file E330640)



## FUSE CHARACTERISTICS



New P/Nr. For UL		CRF110	CRF200	CRF250	CRF300	CRF400	CRF500
Historical P/N	Axial	CRF251-8	CRF252-8	CRF253-8	CRF254-8	CRF256-8	CRF257-8
	SMD	RZS1	RZS2	RZS3	RZS4	RZS6	-----
Resistance Range	230[V]			10R ... 330R	10R ... 330R	10R ... 330R	
	375[V]	1R ... 100R	1R ... 240R				1R ... 330R
	120[V]			10R ... 90R	10R ... 90R	10R ... 90R	
	170[V]	1R ... 100R	1R ... 240R				1R ... 330R

New P/Nr. For Standard		CRF110	CRF200	CRF250	CRF300	CRF400	CRF500
Historical P/N	Axial	CRF251-4	CRF252-4	CRF253-4	CRF254-4	CRF256-4	CRF257-4
Resistance Range		*1R ... 100R	*1R ... 240R	*1R ... 330R	*1R ... 470R	*1R ... 330R	*1R ... 330R

**Note:** The special construction off resistance values >10R results in an immediate interruption (<1s, 200[ms] typical), when mains voltage (120/230[V]<sub>RMS</sub>) is applied. No flames, no explosion. After fusing, the resistance value > 100K.


\* The interruption mechanism for resistance values <10R and resistance values >max. range is not clearly defined, also for other voltage.

Need to be tested in the final application




# CRF Series Datasheet

Precision Fusible Safety Wirewound Resistors | Axial and SMD Version  
 Ceramic core | Flame retardant coating | UL1412 Recognized (file E330640)




## PACKAGING

The standard packaging for CRF in axial type is taped, dimensions below.



Type	Historical P/N:	Pack Code	Forming Type (Inner Taping dim.)	A	C	S	SPQ
<b>CRF110</b>	CRF251-4 / -8	T = Taped Ammo pack	52-	52	65	5	1000
<b>CRF200</b>	CRF252-4 / -8			52	65	5	1000
<b>CRF250</b>	CRF253-4 / -8		73-	73	85	10	1000
<b>CRF300</b>	CRF254-4 / -8			73	85	10	1000
<b>CRF400</b>	CRF256-4 / -8			73	85	10	1000
<b>CRF500</b>	CRF257-4 / -8			73	85	10	500



## SMD LEAD CONFIGURATIONS



Type	Historical P/N	Size	L	L <sub>1</sub> max.	ØD max.	Ød ±0,05	E	Z max	l	a	b
<b>CRF110</b>	RZS1	5315	13,4±0,5	9,0	3,0	0,65	5,0±0,5	7,0	10	10	10
<b>CRF200</b>	RZS2	5315		9,7	4,0	0,80					
<b>CRF250</b>	RZS3	6720	17,0±1,0	14,5	4,5	0,65		7,5	14		
<b>CRF300</b>	RZS4	6720		12,6	6,0	0,80					
<b>CRF400</b>	RZS6	8424	20,9±1,0	17,0	6,0	0,80		8,0	16		

# CRF Series Datasheet


Precision Fusible Safety Wirewound Resistors | Axial and SMD Version  
 Ceramic core | Flame retardant coating | UL1412 Recognized (file E330640)



Type	A0	B0	W	D1	P	T2
CRF110 CRF200	5,0	13,7	24	2,0	8	7,2
CRF250 CRF300	5,7	16,7	24	2,0	8	7,6
CRF400	6,0	21,4	32	2,0	12	8,1

Type	W1	W2	N	A
CRF110 CRF200	25,4	29,5	90	330
CRF250 CRF300				
CRF400				

Type	Packaging	SPQ
CRF110 CRF200 CRF250 CRF300	13(inch) Blister tape	1000
CRF400	15(inch) Blister tape	



## Ordering Code for SMD:

CRF	300	J	K	-	ZB-	150R	UL
Serie	* Power rating	Tol.	Pack-Code	TCR	Forming type	R Value	Special
		J = ±5%	K = Blister Tape Reel	- Base on spec.	ZB- Z version		UL = UL Version

## ALTERNATIVE LEAD CONFIGURATIONS

This type CRF is also available in a different pre-forming, as shown below, other's upon request.

### THOUGH HOLE VERSION

Axial Goal Post (AG-)	Axial Goal Post Kink (AK-)	Radial (RD-)	Radial 2 Kink (RK-)

# CRF Series Datasheet

Precision Fusible Safety Wirewound Resistors | Axial and SMD Version  
Ceramic core | Flame retardant coating | UL1412 Recognized (file E330640)

## Legal Disclaimer Notice

### DISCLAIMER

VITROHM, its distributors and agents, hereby disclaims all liabilities for any errors, inaccurate or incompleteness contained in any product related information, including but not limited to product specifications, datasheets, pictures and/or graphics.

VITROHM may make changes, modifications and/or improvements to product related information at any time and without notice.

VITROHM makes no representation, warranty, and/or guarantee regarding the suitability of the product for any particular purpose or the continuing production of any of its products. To the maximum extent permitted by law, VITROHM disclaims all liability arising out of the application or use of any VITROHM product all liability, including without limitation special, consequential, or incidental damages, and all implied warranties, including warranties of fitness for a particular purpose, non-infringement, and merchantability.

YAGEO Corporation and its affiliates do not recommend the use of commercial or automotive grade products for high reliability applications or manner space flight.

VITROHM products are not designed for use in lifesaving or life-sustaining applications or any application in which the failure of VITROHM product could result in personal injury or death. Customers using or selling VITROHM products not expressly indicated for use in such applications do so at their own risk.

Although VITROHM design and manufactures its products to the most stringent quality and safety standards, isolated component failures may still occur. Accordingly, customer applications which required a high degree of reliability or safety should employ suitable designs or other safeguards (such as installation of protective circuit or redundancies) to ensure that the failure of an electrical component does not result in a risk or personal injury or property damage.

Statements of suitability of products are based on VITROHM knowledge of typical operating conditions for such applications but are not intended to constitute – and VITROHM specifically disclaims – any warranty concerning suitability for a specific customer application or use. Parameters provided in this datasheet may vary in different applications and performance may vary over time. This information is intended for use only by customer who have the requisite experience and capability to determine the correct products for their application. The customer is responsible for checking and verifying the extent to which the information contained in this datasheet is applicable to an order at the time the order is placed. All information given herein is believed to be accurate and reliable, but it is presented without guarantee, warranty, or responsibility of any kind, expressed or implied.

Even under VITROHM recommended storage conditions, solderability on the terminals out of recommended storage time may be degraded. It is strongly recommended to confirm solderability before using VITROHM products of which storage time is exceeding the recommended storage time.

When disposing VITROHM products, please dispose them properly using an authorized waste company. Before purchasing or using VITROHM products, please confirm the latest information with a VITROHM sales representative.