

## A50DQ4470AA60K

Aliases (50DQ4470AA60K)

A50, Film, Metallized Polyester, Automotive Grade, 4.7 uF, 10%, 63 VDC, 40 VAC, 85°C



Click [here](#) for the 3D model.

Dimensions	
D	9.5mm MAX
L	28mm MAX
LL	40mm +/-5mm
F	0.8mm +/-0.05mm

  

Packaging Specifications	
Packaging	Bulk, Bag
Packaging Quantity	500

General Information	
Series	A50
Dielectric	Metallized Polyester
Style	Axial
Features	Automotive Grade
RoHS	Yes
Lead	Wire Leads
Qualifications	AEC-Q200
Typical Component Weight	2.6 g
Miscellaneous	Above 85C DC And AC Voltage Derating Is 1.25%/C. maxKO = 190.

Specifications	
Capacitance	4.7 uF
Tolerance	10%
Voltage DC	63 VDC, 47.25 VDC (105C)
Voltage AC	40 VAC
Temperature Range	-55/+105°C
Rated Temperature	85°C
Dissipation Factor	0.8% 1kHz, 1.2% 10kHz
Insulation Resistance	212.8 MOhms
Max dV/dt	1.5 V/us
Inductance	7 nH

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.